







**HEADER PRESS-IN PIN 0.6x0.6 MM
PIN SPACING 2.5 MM / 0.098 IN 100%
PROTECTED AGAINST MISMATING
MATING**

733-332/100-000 TO 733-342/100-000

PDF DATASHEET

© 1992 - 2011 CADENAS GmbH

ITEM-NO. (ITEM-NO.)	733-338/100-000
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	4
RM (PIN SPACING / mm)	2.5
P (NO. OF POLES)	8
Height (Height / mm)	8.9
Width (Width / mm)	22.5
Depth (Depth / mm)	7.8
COLOR (COLOR)	lichtgrau
Comment (Comment)	L = (No. of poles + 1) x Pin Spacing
Dimensions (Dimensions)	1,1 +0,1 mm