

Item no.: 288-364
Product description: SWITCHING RELAY MODULE RELAY DIRECT SOLDERED
RELAY WITH 1 MAKE CONTACT (1a)



Produkt kann von Bild abweichen / product may differ

Packing unit 1 piece

Product group	6 (Electronics)
Coil voltage DC	24 V
Contact material	AgNi 0.15 + HV
max. switching voltage	AC/DC 250 V
max. make current	4 s 16 A
max. break current	8 A
max. continuous current	6 A
max. switching power (resistive) VA	1500 VA
max. switching power (resistive) W	100 W
Pull-in power	240 mW
Operating power	500 mW
Pull-in time (typ)	4 ms
Drop-out time (typ)	0 ms
Bounce time (typ)	2 ms
Dielectric strength contact / coil (kV)	4 kV
Nominal voltage acc. to VDE 0110/1.89	250 V / 4 kV / 3
Mechanical life	30 x 10 ⁶ switching operations
Mechanical life at max. resistive load AC	2 x 10 ⁵ switching operations
Ambient operating temperature	-25 °C ... +40 °C
Current consumption (Un) (Coil 20 °C)	16 mA

Cross section [mm²]
Cross section [AWG]

0.08 - 2.5 mm²
28 - 12 AWG



Connection method	CAGE CLAMP® CONNECTION
Weight	30.6 g
Color	gray
Height	47 mm
Height	1.85 in
Width	13 mm
Width	0.512 in
Depth	85 mm
Depth	3.346 in
Strip length from	5 mm
Strip length to	6 mm
Strip length	0.22 in
Mounting	TS 35

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected