

You are here: eServices & Applied Computing > Display Solutions > ES-1000 LCD Kits > **ES-1108R-LSAE**

ES-1108R-LSAE

Print page | Email page

8.4" Color TFT-LCD Kit for LVDS Interface with 4-wire Resistive Touch Screen Kit



MainFeatures

- LCD Panel: AUO G084SN05 V1
- Display: 800 x 600 SVGA, 262K
- Viewing Angle (L/R/U/D): 60/60/60/40
- Brightness (nit): 280
- Response Time (ms): 35
- Backlight (hrs.): CCFL, 2-tubes, 50,000 hrs
- Operation Temp.: 0 ~ 50 °C
- ES-1108R-LSA-01E ~ 04E LCD Kit Cable Length (mm): 500 (optional)
- Touch Screen Kit: Pre-installed 4-wire Resistive Touch screen kit
- Outline Dimensions mm (W x H x D): 203 x 142.5 x 9.8



Introduction

8.4" Color TFT-LCD Kit for LVDS Interface with 4-wire Resistive Touch Screen Kit

Ordering Information	
Part Number	Description
ES-1108R-LSAE	8.4" LCD kit,AUO 280 nites,LVDS,SVGA w/
ES-1108R-LSA-01E	8.4" LCD kit,AUO 280 nites,LVDS-1,SVGA
ES-1108R-LSA-03E	8.4" LCD kit,AUO 280 nites,LVDS-3,SVGA
ES-1108R-LSA-04E	8.4" LCD kit,AUO 280 nites,LVDS-4,SVGA
ES-1108R-LSA-02E	8.4" LCD kit,AUO 280 nites,LVDS-2,SVGA

Contact Information		
Office	Tel	Email
Advantech North & South America	1-888-576-9668	ePinfo@advantech.com
Advantech Europe Customer Care Center	00 800 24 26 80 80	customercare@advantech.eu
Advantech Headquarters	886-2-2792-7818	MKT.eVideo@advantech.com.tw

Rate this page :

Did the information help you achieve your goal?

☐ Yes ☐ No

Your eMail address:

Your Country:

Afghanistan

Please provide us with comments to help improve this page:

Submit

Find Resources

Datasheet (PDF)

Downloads

Driver

Online Catalog

Newsletter Subscribe

Services

Buy Online

Feature Articles

Industrial Computer

Tools

Add to Del.icio.us

DIGG this!

Google bookmark

Yahoo! My Web

Technorati