

Search Results

- Evaluate
 - FAQ's
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) [Search Tips](#) 

Text Search: 'F9PE10R-NM15'

Your search criteria matched only one product, shown below

F9PE10R-NM15



- Pass all TIA/EIA-568-B.3 performance requirements
- 100% factory inspected end face geometry in compliance with Telcordia GR-326-CORE, Issue 3
- Typical insertion loss per connection: 0.25dB
- UPC polished (55dB minimum return loss)
- Include color-specific keys with positive and negative keying features to visually and mechanically distinguish connections to prevent unauthorized mating with unlike keyed or non-keyed adapters
- Part of a complete keyed LC system that includes Opti-Core® Patch Cords and Pigtails, OptiCam® Pre-Polished Cam Connectors, Opticom® Fiber Adapter Panels (FAPs) and Mini-Com® Adapter Modules
- Factory terminated and 100% tested for insertion loss and return loss
- Insertion loss and return loss data recorded for every singlemode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber

Additional lengths and availability: Keyed LC patch cords and pigtails are available in 1m – 10m lengths in 1m increments, and 15m, 20m, and 30m lengths. For other lengths, contact Customer Service for actual lead times.

Additional keyed colors include the following: G–Violet, H–Aqua, J–Rose, K–Slate, L–Brown, P–White, Q–Charcoal, R–Lavender, S–Peach, T–Steel Blue, V–Maroon and W–Mint.

▪ Part Number	F9PE10R-NM15
▪ RoHS Compliance Status	Compliant
▪ Note	Intended for use in fixed installations which are outside the scope of RoHS.
▪ Part Description	LC (keyed P – Lavender) to pigtail singlemode duplex pigtail, 1.6mm jacketed cable (one duplex keyed LC connector on one end and open on the other end) – 9/125µm.
▪ Product Type	Keyed LC Patch Cords
▪ Length (m)	15
▪ Fiber Compatibility	9/125µm
▪ Fiber Cable Size	1.6mm
▪ Fiber Cable Type	Jacketed
▪ Fiber Type	Singlemode
▪ Connector 1 Type	LC Connector - Keyed P - Lavender
▪ Connector 2 Type	Pigtail
▪ Flammability Rating	Plenum (OFNP)
▪ Key Type and Color	Keyed R - Lavender
▪ Pricing Description	LC (keyed R - Lavender) to pigtail 9/125µm singlemode, duplex patch cord, 1.6mm jacketed cable, 15M
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

[Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.](#)