


# FLEXIBLE PIN COUNT TIGER EYE™ SOCKET

(1.27 mm) .050" PITCH • SFMC SERIES

MAX  
2.9  
A m p s

8  
G b p s



## SFMC Board Mates: TFM

Cable Mates:  
FMTP, FFMD\*

\*Note: Standard FFMD callout will not mate with FLE, SFMC. Must use gold plated callouts. (See drawing on web.)

| SFMC | 1 | NO. PINS PER ROW | LEAD STYLE | PLATING OPTION | D | OPTIONS |
|------|---|------------------|------------|----------------|---|---------|
|------|---|------------------|------------|----------------|---|---------|

02 thru 50

-01, -03  
= Through-hole

-L1, -L3  
= Low Insertion Force Through-hole

-02  
= Surface Mount

-L2  
= Low Insertion Force Surface Mount

-T1  
= Through-hole Tiger Eye™ LITE

-T2  
= Surface Mount Tiger Eye™ LITE

-F  
= Gold flash on contact, Matte Tin on tail

-L  
= 10 μ" (0.25 μm) Gold on contact, Matte Tin on tail

-K  
= (4.00 mm) .157" DIA Polyimide film Pick & Place Pad (4 positions min.)

-P  
= Plastic Pick & Place Pad (5 positions min.)

-TR  
= Tape & Reel

-FR  
= Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks)

## SPECIFICATIONS

**Insulator Material:**  
Black Liquid Crystal Polymer

**Contact Material:**  
Tiger Eye™ = BeCu  
Tiger Eye™ LITE = Phosphor Bronze

**Plating:**  
Au or Sn over 50 μ" (1.27 μm) Ni

**Current Rating:**  
2.9 A per pin (2 pins powered)

**Voltage Rating:**  
219 VAC/310 VDC

**Operating Temp Range:**  
-55 °C to +125 °C

**Insertion Depth:**  
(3.05 mm) .120" to (4.06 mm) .160"



**Max Cycles:**  
10,000 with 30 μ" (0.76 μm) Au

## PROCESSING




**Lead-Free Solderable:**  
Yes

**SMT Lead Coplanarity:**  
(0.10 mm) .004" max (02-26)  
(0.15 mm) .006" max (27-50)\*

\*(.004" stencil solution may be available; contact ipg@samtec.com)



-P OPTION



**ALSO AVAILABLE**  
Contact Samtec

Other plating

| LEAD STYLE    | A           | B           |
|---------------|-------------|-------------|
| -01, -L1, -T1 | (3.05) .120 | (0.51) .020 |
| -03, -L3      | (1.91) .075 | (0.41) .016 |

**Note:**  
Some lengths, styles and options are non-standard, non-returnable.

View complete specifications at: [samtec.com?SFMC](http://samtec.com?SFMC)