







ITEM	DESCRIPTION
1	SCREW
2	EXTERNAL THREAD COVER
3	INSERT
4	GASKET
5	GROMMET
6	EXTERNAL THREAD NUT

C28200NOR****

SERIES _____
C28= EXTERNAL THREAD FORM A
POLES _____
2= 2 POLE & 3= 3 POLE
THREAD _____
00 = EXTERNAL THREAD
MATERIAL AND HOUSING COLOR _____
G= PA6 GRAY, N= PA6 BLACK, W= PA6 BLACK UL V0, T=TRANSPARENT
GROUND POSITION _____
0= UNMOUNTED, 2= H12, 3=H3, 6 =H6 & 9= H9
SCREW AND GASKET _____
R= INTEGRATED NBR GASKET AND IP67 SCREW
S= INTEGRATED SILICONE GASKET AND IP67 SCREW
T= PROFILE NBR GASKET AND IP67 SCREW
NON STANDARD PACKAGING _____
CN= BULK PACK UN-MOUNTED
SN= BULK PACK MOUNTED
67= NEUTRAL PACKAGING
CF= BULK PACK FULLY MOUNTED
ADDITIONAL CODES _____
SA= UL AGENCY APPROVED

NOTES:

1. FOR SPECIFIC PART NUMBERS PLEASE CONTACT SALES
OR CONSULT THE INTELLIGENT PART NUMBERS IN THE TABLE ATTACHED

2. PRODUCT SPEC: SEE PS-121201-001


3. PACKAGING SPEC: SEE PK-121201-001

4. CABLE SIZES 4 - 9 mm DIAMETER

5. TIGHTENING TORQUE: SEE PS-121201-001

6. GROUND POSITION SHOWN H12

LAST INSPECTION NUMBER USED 8

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
QUALITY SYMBOLS		EC NO: 119342 DRWN: AFAWLAK01 CHK'D: CHKD: APPR: DIMAHER		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex® TYPE A ASSEMBLY SERIES 121201		
▽ = 0 ▽ = 0 ▽ = 0 ▼ = 0 ▽ = 0 ⊠ = 0 ■ = 0 ▽ = 0				ANGULAR TOL ± °		MM	1:1					
		2017/07/13		2017/09/08		DRWN BY		DATE		PRODUCT CUSTOMER DRAWING		
						DSHEA		2013/11/05				
						CHK'D BY		DATE		SERIES 121201		
						SMCGREEVY		2013/11/05				
						APPR BY		DATE		MATERIAL NUMBER SEE TABLE		
						STGRIFFIN		2013/11/18				
						DRAWING SIZE		THIRD ANGLE PROJECTION		CUSTOMER GENERAL MARKET		
						A2						
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				DOCUMENT NUMBER SD-121201-003		
										DOC PART 001		

