



REVISIONS				
P	LYR	DESCRIPTION	ECN	DATE
0		作成 (RELEASED)	FJ00-1109-97	30 JUL 97



注記
△ [-Z-] 面より8.5mmの位置で測定
2 推奨取付ねじ: JIS B1115, B1122 タップねじ, なべ2種
呼び径3, 長さ6mm以下 (締付けトルク: 0.4N.m (4Kg-cm) 以下)
NOTE
△ MEASURED AT THE SECTION 8.5mm FROM [-Z-]
2 RECOMMENDED SCREW: PAN-HEADED, TYPE 2 TAPPING SCREW
OF 3DIA X 6LEN(MAX) (JIS B1115, B1122)
(FASTENING TORQUE FOR SCREW: 0.4N.m (4Kg-cm) MAX)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		AMP Kawasaki, Japan	
DIMENSIONS: 単位: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED	
MATERIAL: HOUSING: PBT, CONTACT: BRASS		FINISH: HOUSING: GRAY, CONTACT: PRE-TIN	
WEIGHT: 50.5g		CUSTOMER DRAWING	
DRAWING NO: 411-5828 (-1)		DRAWING NO: 411-5828 (-1)	
SIZE: A2		CAGE CODE: 00779	
SCALE: 1-1		SHEET: 1 OF 1	