




REV. 0

DCO 17483


COIL: @ 25°C
 RESISTANCE 160 OHMS ±10%
 NOMINAL VOLTAGE 12.0 VDC
 MUST OPERATE 6.4 VDC
 MUST RELEASE 0.7 VDC

ENVIRONMENT:
 VIBRATION 10 Hz TO 3000 Hz @ 20 g's
 SHOCK 100 g's 6±1 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES:

CUSTOMER DATA SHEET

BLUE BEAD



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
2A 28 VDC RESISTIVE
100,000 OPERATIONS

DR. DS 1/15/02 CK. TIG 01-15 -02

CII Technologies
 advanced control electronic solutions

CUST. C.I.I. STD

CUST. NO. _____ REV. _____

"HFW" RELAY

HFW1206G00