


CSC10T


10 mm


50 x 75 mm

18 mm

Polyamide 6.6

2 spring clamps & 2 slots for interconnection

		UL ^①
16-6AWG	1.5-10sq.mm	16-6AWG
600 V	800 V	600 V
65 A	57 A	65 A


CSC16T


12 mm

45 x 72 mm

20 mm

Polyamide 6.6

2 spring clamps & 2 slots for interconnection

		UL ^①
16-4AWG	1.5-16sq.mm	16-4AWG
600 V	800 V	600 V
85 A	76 A	85 A


CSC2.5T1-2


5 mm

36 x 74 mm

15 mm

Polyamide 6.6

3 spring clamps & 2 slots for interconnection

C SP US	VDE	C E220514 US
22-14AWG	0.5-2.5sq.mm	22-14AWG
600 V	800 V	600 V
20 A	24 A	20 A


CSC2.5T2-2


5 mm


36 x 90 mm

15 mm

Polyamide 6.6

4 spring clamps & 2 slots for interconnection

C SP US	VDE	C E220514 US
22-14AWG	0.5-2.5sq.mm	22-14AWG
600 V	800 V	600 V
20 A	24 A	20 A


CSC4T1-2


6 mm

42 x 85 mm

13 mm

Polyamide 6.6

3 spring clamps & 2 slots for interconnection

C SP US	VDE	C E220514 US
22-12AWG	0.5-2.5sq.mm	22-12AWG
600 V	800 V	600 V
25 A	32 A	25 A



Cat. No.	Std. Pk.
CSC10T	50
EPCSC10T	50

Cat. No.	Std. Pk.
CSC16T	50
EPCSC16T	50

Cat. No.	Std. Pk.
CSC2.5T1-2	100
EPCSC2.5T1-2	50

Cat. No.	Std. Pk.
CSC2.5T2-2	50
EPCSC2.5T2-2	50

Cat. No.	Std. Pk.
CSC4T1-2	50
EPCSC4T1-2	50


CA702
CA802

50
50

CA702
CA802

50
50

CA702
CA802

50
50

CA702
CA802

50
50

CA702
CA802

50
50

CA801/4	100
---------	-----

CA801/5	100
---------	-----

CA801/1	100
CA801/1-3	100

CA901/1 100

CA801/1	100
CA801/1-3	100

CA901/1 100

CA801/2	100
CA801/2-3	100

CA901/2 100

MT10	100
------	-----

MT12	100
------	-----

MT5	100
MT6F	100

MT5	100
MT6F	100

MT6	100
MT6F	100

^① UL recognition in progress.