


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION . 19
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.



1. WIRE INSULATION DIA. = .080-.125
2. 22-18 MARKING FOR MILITARY COMMERCIAL RANGE 22-16

△ TIN PLATE MIL-T-10727 .000100 MIN THK.

REVISIONS				
P	F	ZONE	LTR	DESCRIPTION
✓			E	REDRAWN-REV. PER G-1475, G-1175, P85-0033 & P85-0034
✓			F	OBSOLETE 2-3 PER G-2393
✓			G	REV PER G-4732
✓			H	OBS 2-2 PER G-3779
✓			J	REV PER G-5411

OBSOLETE
OBSOLETE

QUANTITY	DESCRIPTION	PART NO
100	ON TAPE, LG. BOX	32497-1
1000	ON TAPE, REEL	32497-1
5000	LOOSE PIECE	32497

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .005 ANGLES ± .008		CONTRACT NO		NAME	
MATERIAL: NYLON - RED BODY & SLEEVE; COPPER (QQ-C-576)		DR UTA/RFB 9-19-85		AMP AMP INCORPORATED Harrisburg, Pa.	
INSULATION: NYLON - RED		CHK [Signature] 1/9/86		TERMINAL, FLANGED SPADE	
BODY & SLEEVE: COPPER (QQ-C-576)		APPRO [Signature] 1/9/86		P.I.D.G. FLANGED SPADE	
FINISH BODY - 3		APPO		WIRE SIZE: 22-16	
		BSGN APPO		SIZE B	
		OTHER APPO		FSCM NO 00779	
				DRAWING NO 32497	
				SCALE NTS	
				SHEET 1 OF 1	

CUSTOMER DRAWING