



Pin Grid Array Socket/Header on 0.100 [2.54] Centers w/Solder Pin Tails

FEATURES

- Aries offers a wide number of pin grid array configurations from which to choose.
- Low-insertion-force contacts standard.

GENERAL SPECIFICATIONS

- PGM SERIES SOCKET BODY: black UL 94V-0 glass-filled 4/6 Nylon
- PGG SERIES SOCKET BODY: FR-4, 0.062 [1.57] thick
- PIN BODY: Brass 360 1/2-hard per UNS C36000 ASTM-B16-00
- PIN BODY PLATING: either 200μ [5.08μ] min. Sn per ASTM B545 Type 1 or 200μ [5.08μ] min. 93/7 Sn/Pb per ASTM B545 or 10μ [0.254μ] min. Au per MIL-G-45204 over 100μ [2.54μ] min. Ni per SAE AMS-QQ-N-290
- 6-FINGERED COLLET CONTACT: BeCu per UNS C17200 ASTM-B194-01 (not applicable to Post Style Pin)
- CONTACT PLATING: either 100μ [2.54μ] min. Sn per ASTM B545 Type 1 or 100μ [2.54μ] min. 93/7 Sn/Pb per ASTM B545 or 10μ [0.254μ] min. Au per MIL-G-45204 or 30μ [0.762μ] min. heavy Au plating also available
- CONTACT CURRENT RATING: 3 amps
- OPERATING TEMPERATURE : -67°F to 221°F [-55°C to 105°C] Sn plating
: -67°F to 257°F [-55°C to 125°C] Au plating
- STANDARD CONTACT INSERTION FORCE : 67g/pin
WITHDRAWAL FORCE : 30g/pin
NORMAL FORCE : 45g/pin; based on a 0.018 [0.46] dia. test lead
- SPECIAL ULTRA-LOW INSERTION FORCE : 22g/pin
WITHDRAWAL FORCE : 11g/pin
NORMAL FORCE : 12g/pin; based on a 0.018 [0.46] dia. test lead
- ACCEPTS LEADS: 0.015-0.026 [0.38-0.66] in dia., from 0.110 [2.79] long min.

MOUNTING CONSIDERATIONS


- SUGGESTED PCB HOLE SIZE : SOLDER TAIL : 0.030 ±0.002 [0.76 ±0.05] dia.
: POST STYLE : 0.028 ±0.002 [0.71 ±0.05] dia.



CUSTOMIZATION: In addition to the standard products shown on this page, Aries specializes in custom design and production. Special materials, platings, sizes, and configurations can be furnished, depending on the quantity. **NOTE:** Aries reserves the right to change product general specifications without notice.

ORDERING INFORMATION

Consult Factory – Aries will assign a special P/N



ALL DIMENSIONS: INCHES [MILLIMETERS]

ALL TOLERANCES: ±0.005 [0.13] UNLESS OTHERWISE SPECIFIED

BASIC DIMENSIONS :

"A SQ MAX" # PINS PER ROW x 0.100 [2.54]

"B" (# PINS PER ROW -1) x 0.100 [2.54]

ADDITIONAL CONFIGURATION OPTIONS INCLUDE A CUT-OUT WINDOW FOR MORE EFFICIENT UTILIZATION OF BOARD SPACE AND BETTER COOLING – AVAILABLE WITH OR WITHOUT PIN NUMBER ONE IDENTIFICATION SHOWN BELOW.

CONSULT FACTORY FOR OTHER SIZES AND CONFIGURATIONS



ARIES
ELECTRONICS, INC.

Bristol, PA 19007-6810 USA
TEL (215) 781-9956 • FAX (215) 781-9845
WWW.ARIESELEC.COM • INFO@ARIESELEC.COM



14033
1 of 2
Rev. AA



Pin Grid Array Socket/Header on 0.100 [2.54] Centers w/Solder Pin Tails

SOLDER TAIL



POST STYLE



ORDERING INFORMATION

XXX-PXX XX XXX-X X

No. of Pins

Series Designator

PGM = Molded Housing (7x7 thru 18x18)

PGG = FR-4 Housing (3x3 thru 6x6, 19x19 and above)

Grid Size

Footprint Number (assigned by factory)

Optional Plating

0 = Au Contact/Sn Shell (Post style all Sn)

0T = Sn Contact/Sn Shell

0H = Heavy Au Contact/Sn Shell

1 = Au Contact/Au Shell (Post style all Au)

1H = Heavy Au Contact/Au Shell

* 1U = Au-plated Ultra-low Insertion Force Contact/Au Shell

* OTL = Au Contact/Sn/Pb Shell

* OTLTL = Sn/Pb Contact & Shell

* OHTL = Sn/Pb Shell

* Special Order, Consult Factory


Pin Style

1 = Solder Pin Tail

4 = Post Style - 0.025 [0.64] diameter

5 = Post Style - 0.018 [0.46] diameter

TOP VIEW



SPECIAL FOOTPRINT INSTRUCTIONS:

1. Make a copy of this sheet.
2. Fill in circles for footprint desired using the key below.
3. Fill in the information below, including Style and Plating options.
4. Send to Aries for a prompt quotation.

COMPANY NAME _____

ADDRESS _____

CITY _____

REQUESTED BY _____

PHONE _____

DATE _____

PIN STYLE _____

PIN PLATING _____

○ = No pins

● = Pins

⊗ = Plugged holes*

* Plugged holes are for PGA ZIF sockets only.

Consult **Data Sheets 10004** and **10005** for details.



ARIES
ELECTRONICS, INC.

Bristol, PA 19007-6810 USA

TEL (215) 781-9956 • FAX (215) 781-9845

WWW.ARIESELEC.COM • INFO@ARIESELEC.COM



14033

2 of 2

Rev. AA

PRINTOUTS OF THIS DOCUMENT MAY BE OUT OF DATE AND SHOULD BE CONSIDERED UNCONTROLLED