

PRODUCT NO.

SEE TABLE

PRODUCT NO.	STAND OFF DIM "M"(mm)	HOLD DOWN
92791-XXXX		
001	0	NONE
001MLF	0	NONE
△ 001LF	0	NONE
001H	0	YES
△ 001HLF	0	YES
011	0	NONE
021	2	NONE
△ 021LF	2	NONE
041	4	NONE
△ 041LF	4	NONE
△ 041H	4	YES
△ 041HLF	4	YES
051	5	NONE
△ 051M	5	NONE
△ 051LF	5	NONE
△ 051H	5	YES
△ 051HLF	5	YES
△ 052 ⊕	5	NONE
053M	5	NONE
△ 022LF	2.2	NONE
△ 022	2.2	NONE
△ 043LF	4.3	NONE
△ 043	4.3	NONE

92791-XXXXXX

OPTIONAL HOLD DOWN

⊕
OPTIONAL FOR TWO TYPE
COVER PLATE ("S")△
LOW COST VERIOSN

FOR LOWER OR UPPER DECK

STAND OFF HEIGHT
(DIM "M")

MOUNT STYLE TO PCB

NONE : N O

H : YES(SEE FIGURE OF -XXXH)

NONE "S": 93328-001 (EXCEPT 92791-052)

S (P/N WITH "S"): 72228-003

NONE : N O

M: YES

1 : AVAILABLE FOR BOTH DECKS

NONE : NOT AVAILABLE FOR BOTH DECKS




0 : 0mm(NONE)

2 : 2mm 22: 2.2mm

4 : 4mm 43: 4.3mm

5 : 5mm

0 : AVAILABLE FOR BOTH MOUNT

92791-xxxH
(OPTIONAL HOLD DOWN)TYP.(2)
HOLD DOWN

HOLD DOWN

ONLY FOR 92791-053M

mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		PCMCIA
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
H	N06-0065	MZ	03/22/08	angles	linear	MM	68P LONG HEADER TYPE I/II /III
J	N06-0129	MZ	05/10/08			scale 4	GUIDE ASSY
K	N07-0109	DT	4/25/07	±2°			
L	N07-0219	MZ	1/7/08	dr	Mike Zhou	05/10/08	dwg no 92791 sheet 1 of 2 size A 4
M	N08-0219	MZ	11/20/08	enrg	Mike Zhou	05/10/08	
				chr	Mike Zhou	05/10/08	type CUSTOMER Drawing
				appd	Qin David	05/10/08	
sheet index	revision sheet	M	M				
		1	2				


FCI CONFIDENTIAL



FCIconnect.com

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI.
Copyright FCI

PRODUCT NO.
92791-001
92791-001LF
92791-001H
92791-001HLF
92791-021
92791-021LF
92791-041
92791-041LF
92791-041H
92791-041HLF
92791-051
92791-051M
92791-051LF
92791-051H
92791-051HLF
92791-052
92791-022LF
92791-043
92791-043LF
92791-011
92791-001M
92791-053M



- NOTE
- ① MATERIAL
 - GUIDE : POLYPHTHARAMID UL94V-0 BLACK
 - PLATE : STAINLESS
 - EMI CONTACT : PHOSPHOR BRONZE
 - HOLD DOWN : BRASS
 - ② FINISH
 - EMI CONTACT : PRE-PLATING
 - 0.5 μ m MIN. Ni OVER ALL UNDER PLATING
 - 0.5 μ m MIN. Au CONTACT AREA
 - ③ "M" SHOWS IT IS LOW COST VERSION, IT IS OPTIONAL AND IN FIRST OF LETTER OF PART NO., SUCH AS 92791-051M IS LOW COST VERSION
DETAIL AS COMPONENT INFORMATION, 92791-051 IS NOT LOW COST VERSION.
 - 4. GENERAL TOLERANCE : ± 0.3

mat'l. code				surface	tolerance	projection	product family			
				ISO 1302	ISO 406 ISO 1101		PCMCIA			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title			
M				angles	linear	MM	68P LONG HEADER TYPE I / II / III			
				$\pm 2^\circ$		scale 4	GUIDE ASSY			
				dr	Mike Zhou	05/10/06	dwg no		sheet 2 of 2	size
				enr	Mike Zhou	05/10/06	92791		A 4	
				chr	Mike Zhou	05/10/06	type		CUSTOMER	Drawing
				appd	Qin David	05/10/06				
sheet	revision									
index	sheet									