

GRIP TECH HANDHELD ENCLOSURES

This rugged family of hand held cases features interchangeable rubber side grips for easy gripping and a tactical feel and Quick-Snap® battery compartments to speed assembly. These cases are virtually indestructible.



Grip Tech line of Polycarbonate Cases

Grip Tech Series

DIMENSION (IN.)	L	W	H
T-CASE 200 SERIES			
SMALL	7.4	4.8	1.9
MEDIUM	8.3	4.8	2.0
LARGE	9.4	5.5	2.0
EXTREME 300 SERIES			
SMALL	6.5	4.7	1.9
MEDIUM	7.9	4.9	2.1
LARGE	10.5	5.2	2.1
SLOPE 400 SERIES			
SMALL	7.4	4.3	1.9
MEDIUM	8.5	4.9	1.9
LARGE	10.0	5.5	2.3
WEDGE 500 SERIES			
SMALL	7.1	4.3	1.9
MEDIUM	9.0	4.3	1.9
LARGE	10.2	4.9	1.9

- Black and White. Custom colors available.
- NEMA 4 Sealing kit included
- Polycarbonate Material
- Fire Retardant UL 94 V2 Rated
- Color Side Grip Options
 - White, Beige, Red, Orange, Yellow, Black, Blue, Green, Gray
- 6 Assembly Screws with Brass inserts for tight sealing
- Quick-Snap® Interchangeable Battery Compartments
 - 2AA, 4AA, 1-9V, 2-9V holders
- Industry Standard LCD windows
 - 16x2, 16x2 compact, 16x4, 20x4, 3.5" TFT LCD Graphics Display

Series	Size	Window			Colour
4	1	1	-	12	BK

	Order Code	Part Number	Description		
Example:	1014450	411 - 12 - BK	Slope 400	Series	7.4 x 4.3 x 1.9
			LCD Window	2 x 16	- Black

Series	2	T-Case - 200 Series
	3	Extreme - 300 Series
	4	Slope - 400 Series
	5	Wedge - 500 Series

Size (In Inches)	T-Case 200 Series		Length	Width	Height
	1	Small	7.4	4.8	1.9
	2	Medium	8.3	4.8	2.0
	3	Large	9.4	5.5	2.0

Extreme 300 Series					
1	Small	6.5	4.7	1.9	
2	Medium	7.9	4.9	2.1	
3	Large	10.5	5.2	2.1	

Slope 400 Series					
1	Small	7.4	4.3	1.9	
2	Medium	8.5	4.9	1.9	
3	Large	10.0	5.5	2.3	

Wedge 500 Series					
1	Small	7.1	4.3	1.9	
2	Medium	9.0	4.3	1.9	
3	Large	10.2	4.9	1.9	

Window (Small & Medium)	0	No window
	1	2 x 16 LCD Window
	2	2 x 16 Compact LCD Window
	3	4 x 16 LCD Window

Window (Large)	0	No window
	1	4 x 20 LCD Window
	2	2 x 16 LCD Window
	3	2 x 16 Compact LCD Window
	4	4 x 16 LCD Window
	5	72 x 51 Graphics Display Window

12 Overall height of the case, 1 is the height of the top and 2 is the height of the base

Colour	BK	Black
	TW	White