



ZF5S-40-01-T-WT

ZF5S-20-01-T-WT



ZF5S-30-01-T-WT

(0.50 mm) .0197"

ZF5S SERIES

FLAT FLEXIBLE CABLE (FFC) SOCKET

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?ZF5S

Insulator Material:

Natural LCP

Contact Material:

Phosphor Bronze

Plating:

Sn over 50 μ " (1.27 μ m) Ni

Weld Tab:

Phosphor Bronze

Operating Temp Range:

-55 °C to +105 °C

Current Rating:


1.8 A per pin
(1 pin powered)

RoHS Compliant:

Yes

Mates with:

FJH



PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.10 mm) .004" max (10-30)

(0.15 mm) .006" max (40-50)*

*(.004" stencil solution may be available; contact IPG@samtec.com)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality




FILE NO. ET11594

ALSO AVAILABLE (MOQ Required)

- Vertical
- Contact top
- Other positions

ZF5S	NO. OF POSITIONS	LEAD STYLE	PLATING OPTION	WT	OPTION
	-10, -15, -20, -25, -30, -40, -43, -50 (Standard sizes)	-01 = Contact Bottom	-T = Matte Tin	-WT = Weld Tab	-K = (3.00 mm) .118" DIA Polyimide Film Pick & Place Pad -TR = Tape & Reel Packaging



Note:
Some sizes, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.