



Where To Buy

Enter Zip Code:

Enter Quantity:

GO

Sta-Kon®

PRINT

Ring Terminal

T&B Catalog Number: F4-38
UPC Number: 78621080363
Status: Active

Description:
Non-Insulated - Brazed Seam Ring Terminal For Wire Range 4 Stud Size 3/8, Met

ROHS SUBMITTAL PACKAGE

Features

- These non-insulated ring terminals are made of electrolytic copper for high cor installed with crimping tools having a single indenter or double indenter (recon Serrated barrel increases grip on wire.

General

Insulation Type	Non-Insulated - Brazed Se
Terminal Series	F
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	4
Stud Size	3/8

Dimension Information

Stock Thickness	.07
A (inches)	1.35
B (inches)	.60
C (inches)	.49
M (inches)	1.06

Specifications

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling

 Tool Charts

Application Tools
Recommended Tool

[Click Here](#)
[WT115A, TBM6, TBM6S, V](#)
[TBM6S](#)

Packaging

Order Multiple	20
Inner Package	20
Outer Package	100
Package Type	Standard
Package Height	3.3
Package Length	4.6
Package Width	3.3
T&B Sold in UOM	Each
T&B Weight Per UOM	2.08 lbs. per 100
Alternate Package Qty	F73

Application Support

 Overview

[Click Here](#)

 Wire Guide Tables

[Click Here](#)