


1/4" Stereo Plugs

171-1300, 171-1301, 171-1302

KOBICONN

1/4" Stereo Plugs



DIMENSIONS IN.

SPECIFICATIONS	
Type:	1/4" stereo
Breakdown Voltage:	500VAC for 1 minute
Insulation Resistance:	100M Ω min. @ 500VDC
Contact Resistance:	50m Ω max.
Cap, Contacts, Terminal B:	nickel plated brass
Pin, Terminals A and C:	nickel plated steel
Sleeve:	brass
Insulators A & B, Body:	ABs resin
Strain Protector:	poly vinyl
Strain Relief:	red (171-1300), black (171-1301), gray (171-1302)

Date Last Revised: 4/18/05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300514

171-1300, 171-1301, 171-1302

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-1302](#) [171-1300](#) [171-1301](#)