


Model 2383 & 2440 Miniature Insulating Binding Post With Double Mounting Base



FEATURES:

- Accepts miniature banana plugs
- #8-32 hex nut and lockwasher included
- Mounts in panels up to 4.8 (.188) thick

MATERIALS:

Insulated Captive Thumb Nut: Brass

Finish: Model 2383 Gold plated brass

Model 2440 Tin plated brass

Insulation: Polycarbonate. Color: One black and one red

Mounting Base: Polycarbonate. Marking: "POMONA ELECTRONICS CALIF.

Insulator: Polycarbonate. One black and one red

Lockwasher: Steel. Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches

Hex Nut: Brass. Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches.

Binding Post: Brass, Alloy 360, 1/2 Hard.

Finish: Gold plated per MIL-G-45204, Type II, Class 00 over electroless nickel pr MIL-C-26074

RATINGS:

Operating Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 1500 VDC Max.

Operating Temperature: +115°C (+239°F) Max.

Current: 5 Amperes

ORDERING INFORMATION: Model 2383-* & 2440-*

*=Color, -0 Black, -2 Red

Ordering Example: 2383-2 Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[2383-0](#) [2440-0](#)