

3

2

1

NUMBER

C-179610




3rd ANGLE PROJECTION

METRIC

179610-1 : 本 ☒

179610-1 : AS SHOWN



注,



材料 錫めっき済磷青銅(板厚0.2)

2 運用製品規格, 108-5408

3 取付運用規格, 114-5179

4 通鎖状端子型番, 179609-1 (折取り部なし)

NOTES,



MATERIAL PRE-TIN PHOS.BRO (THK 0.2)

2 PRODUCT SPEC. ; 108-5408

3 APPLICATION SPEC. ; 114-5179

4 STRIP TERMINAL ; 179609-1 (W/O NOTCH)

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

Copyright © 19__

AMP (Japan) .LTD.

ALL RIGHTS RESERVED.

AMPAMP (JAPAN) , LTD.
Tokyo, Japan

GENERAL TOLERANCE

0<mm≤10 : ±0.2
 10<mm≤30 : ±0.25
 30<mm≤100 : ±0.3
 ANGLES : ±3°

WIRE RANGE

0.05
 ~0.12 mm² (AWG 30-25)

INSULATION DIA.

0.65~1.35mmφ

MATERIAL

SEE NOTE 1

FINISH

SEE NOTE 1

注 1 参照

注 1 参照

SCALE

SIZE

LOC

NUMBER

REV.

SHEET

O RELEASED F300-4024-96

T/F DK 1/2%

LTR REVISION RECORD

DR CHK DATE

DR. T. S. 1/23/96

DE. T. S. 1/23/96

CHK. S. K. 1/23/96

APP. S. K. 1/23/96

NAME CRIMP TYPE II REC. CONTACT (L/P)
 圧着タイプⅡリセコンタクト (レラ状)
 (AMP CTコネクタ 2mmピッチ) (AMP CT CONN. 2mm PITCH)

PRINT DIST

AMP-J
REV. 10/83

CUSTOMER DRAWING