

PCI-7432/7433/7434, cPCI-7432/7433/7434

64-CH Isolated Digital I/O Cards



cPCI-7432



cPCI-7433



cPCI-7434

Features

- Supports a 32-bit 5 V PCI bus (PCI-7432/7433/7434)
- 3U Eurocard form factor, CompactPCI compliant (PICMG 2.0 R2.1) (cPCI-7432/7433/7434)
- 32-CH isolated digital inputs & 32-CH isolated digital outputs (PCI-7432/7432HIR, cPCI-7432)
- 64-CH isolated digital inputs (PCI-7433/7433HIR, cPCI-7433)
- 64-CH isolated digital outputs (PCI-7434, cPCI-7434/7434P)
- Isolation Voltage:
 - 2500 V_{RMS}: PCI-7432/7433/7434
 - 5000 V_{RMS}: cPCI-7432/7433/7434/7434P
- Sink current up to 500 mA on single isolated output
- Isolated input voltage up to 24 V (PCI-7432/7433, cPCI-7432/7433)
- Isolated input voltage up to 50 V (PCI-7432HIR/7433HIR)
- Two external interrupt sources (PCI-7432/7432HIR/7433/7433HIR, cPCI-7432/7432RP/7433)
- Operating Systems
 - Windows 7/Vista/XP/2000/2003 Server
 - Linux
- Recommended Software
 - AD-Logger
 - VB.NET/VC.NET/VB/VC++/BCB/Delphi
 - DAQBench
- Driver Support
 - DAQPilot for LabVIEW™
 - DAQ-MTLB for MATLAB®
 - PCIS-DASK for Windows
 - PCIS-DASK/X for Linux

Introduction

ADLINK's cPCI/PCI-743X series cards are 64-CH high-density digital input and/or output cards that provide a robust 2,500 V isolation protection and are suitable for most industrial applications. The wide input range of the cPCI/PCI-7432 and cPCI/PCI-7433 makes it easy to sense the status of external devices. There are several options for PCI-743X series, such as normal version with input range from 0 to 24 V, as well as HIR version with high input range from 0 to 50 V. The PCI-7433ALC is specifically designed for AC power test system.

The cPCI/PCI-7432 and cPCI/PCI-7434 feature a wide output range from 5 to 35 V, suitable for relay driving and industrial automation applications. The cPCI/PCI-7432 and cPCI/PCI-7433 also provide two interrupt sources on digital input channels, which are easily configurable.

Specifications

Isolated Digital Input

- Number of channels
 - 32 (PCI-7432/7432HIR, cPCI-7432)
 - 64 (PCI-7433/7433HIR, cPCI-7433)
- Maximum input range (Non-polarity)
 - 24 V, non-polarity (PCI-7432/7433, cPCI-7432/7433)
- Digital logic levels: 0 V to 24 V, non-polarity
 - Input high voltage: 5 V to 24 V
 - Input low voltage: 0 V to 1.5 V
- Input resistance
 - 2.4 kΩ @ 0.5 W (PCI-7432, cPCI-7432, cPCI-7433)
 - 2.4 kΩ @ 1 W (PCI-7433)
 - 4.7 kΩ @ 0.5 W (PCI-7432HIR)
 - 4.7 kΩ @ 1 W (PCI-7433HIR)
- Isolation voltage: 2500 V_{RMS}: PCI-7432/7432HIR/7433/7433HIR
5000 V_{RMS}: cPCI-7432/7433
- Interrupt sources: digital input channel 0 & 1
- Data transfers: programmed I/O

Isolated Digital Output

- Number of channels
 - 32 (PCI-7432/7432HIR, cPCI-7432)
 - 64 (PCI-7434, cPCI-7434)
- Output type: open collector Darlington transistor
- Sink current (PCI-7432/7432HIR/7434, cPCI-7434)
 - 500 mA for single channel @ 100% duty cycle
 - 500 mA for all channels @ 20% duty cycle
- Source current (cPCI-7434P)
 - 500 mA for single channel @ 100% duty cycle
 - 260 mA for all channels @ 10% duty

- Power dissipation: Max. 2.25 W per chip (8 DO channels) (PCI-7432/7432HIR/7434, cPCI-7432/7434)
Max. 1.47 W per chip (8 DO channels) (cPCI-7434P)
- Supply voltage: 5-35 V
- Isolation voltage: 2500 V_{RMS}
- Data transfers: programmed I/O

General Specifications


- I/O connector: 100-pin SCSI-II female
- Operating temperature: 0°C to 60°C
- Storage temperature: -20°C to 80°C
- Relative humidity: 5% to 95%, non-condensing
- Power requirements

Device	+5 V
PCI-7432/7432HIR, cPCI-7432	530 mA typical
PCI-7433/7433HIR, cPCI-7433	500 mA typical
PCI-7434, cPCI-7434P	560 mA typical


- Dimensions (not including connectors)
 - 156 mm x 106 mm (PCI-7432 & PCI-7432HIR)
 - 175 mm x 107 mm (PCI-7433, PCI-7433HIR)
 - 156 mm x 106 mm (PCI-7434)
 - 156 mm x 106 mm (PCI-7434P)
 - 160 mm x 100 mm (cPCI-7432/7433/7434)



PCI-7433



PCI-7434



PCI-7432

Terminal Boards & Cables

DIN-100S-01

Terminal Board with One 100-pin SCSI-II Connector and DIN-Rail Mounting (Cables are not included.)

ACL-102100-1

100-pin SCSI-II cable (mating with AMP-787082-9), 1 M

* For more information on mating cables, please refer to P2-61/62.

Note:

Legacy DIN-502S can be replaced by two DIN-50S-01 and ACL-10252-1 (100-Pin to two 50-Pin Cable, 1 M)

Ordering Information

PCI-7432

32-CH Isolated DI & 32-CH Isolated DO Card

PCI-7432HIR

32-CH Isolated DI & 32-CH Isolated DO Card with High Input Range

PCI-7433

64-CH Isolated DI Card

PCI-7433HIR

64-CH Isolated DI Card with High Input Range

PCI-7434

64-CH Isolated DO Card

cPCI-7433

64-CH Isolated DI Card

cPCI-7434

64-CH Isolated DO Card

cPCI-7434P

64-CH Isolated DO Card with Source Current Transistor

Pin Assignment

PCI-7432/7432HIR, cPCI-7432

IDI_0	1	51	IDI_8
IDI_1	2	52	IDI_9
IDI_2	3	53	IDI_10
IDI_3	4	54	IDI_11
IDI_4	5	55	IDI_12
IDI_5	6	56	IDI_13
IDI_6	7	57	IDI_14
IDI_7	8	58	IDI_15
COM1	9	59	COM2
COM1	10	60	COM2
COM1	11	61	COM2
COM1	12	62	COM2
IDI_16	13	63	IDI_24
IDI_17	14	64	IDI_25
IDI_18	15	65	IDI_26
IDI_19	16	66	IDI_27
IDI_20	17	67	IDI_28
IDI_21	18	68	IDI_29
IDI_22	19	69	IDI_30
IDI_23	20	70	IDI_31
COM3	21	71	COM4
COM3	22	72	COM4
COM3	23	73	COM4
COM3	24	74	COM4
N/C	25	75	N/C
IDO_0	26	76	IDO_8
IDO_1	27	77	IDO_9
IDO_2	28	78	IDO_10
IDO_3	29	79	IDO_11
IDO_4	30	80	IDO_12
IDO_5	31	81	IDO_13
IDO_6	32	82	IDO_14
IDO_7	33	83	IDO_15
VDD1	34	84	VDD2
IGND	35	85	IGND
IGND	36	86	IGND
IGND	37	87	IGND
IDO_16	38	88	IDO_24
IDO_17	39	89	IDO_25
IDO_18	40	90	IDO_26
IDO_19	41	91	IDO_27
IDO_20	42	92	IDO_28
IDO_21	43	93	IDO_29
IDO_22	44	94	IDO_30
IDO_23	45	95	IDO_31
VDD3	46	96	VDD4
IGND	47	97	IGND
IGND	48	98	IGND
IGND	49	99	IGND
+5Vout	50	100	+5Vout

PCI-7433/7433HIR, cPCI-7433

IDI_0	1	51	IDI_8
IDI_1	2	52	IDI_9
IDI_2	3	53	IDI_10
IDI_3	4	54	IDI_11
IDI_4	5	55	IDI_12
IDI_5	6	56	IDI_13
IDI_6	7	57	IDI_14
IDI_7	8	58	IDI_15
COM1	9	59	COM2
COM1	10	60	COM2
COM1	11	61	COM2
COM1	12	62	COM2
IDI_16	13	63	IDI_24
IDI_17	14	64	IDI_25
IDI_18	15	65	IDI_26
IDI_19	16	66	IDI_27
IDI_20	17	67	IDI_28
IDI_21	18	68	IDI_29
IDI_22	19	69	IDI_30
IDI_23	20	70	IDI_31
COM3	21	71	COM4
COM3	22	72	COM4
COM3	23	73	COM4
COM3	24	74	COM4
N/C	25	75	N/C
IDI_32	26	76	IDI_40
IDI_33	27	77	IDI_41
IDI_34	28	78	IDI_42
IDI_35	29	79	IDI_43
IDI_36	30	80	IDI_44
IDI_37	31	81	IDI_45
IDI_38	32	82	IDI_46
IDI_39	33	83	IDI_47
COM5	34	84	COM6
COM5	35	85	COM6
COM5	36	86	COM6
COM5	37	87	COM6
IDI_48	38	88	IDI_56
IDI_49	39	89	IDI_57
IDI_50	40	90	IDI_58
IDI_51	41	91	IDI_59
IDI_52	42	92	IDI_60
IDI_53	43	93	IDI_61
IDI_54	44	94	IDI_62
IDI_55	45	95	IDI_63
COM7	46	96	COM8
COM7	47	97	COM8
COM7	48	98	COM8
COM7	49	99	COM8
N/C	50	100	N/C

PCI-7434, cPCI-7434

IDO_0	1	51	IDO_8
IDO_1	2	52	IDO_9
IDO_2	3	53	IDO_10
IDO_3	4	54	IDO_11
IDO_4	5	55	IDO_12
IDO_5	6	56	IDO_13
IDO_6	7	57	IDO_14
IDO_7	8	58	IDO_15
VDD1	9	59	VDD2
IGND	10	60	IGND
IGND	11	61	IGND
IGND	12	62	IGND
IDO_16	13	63	IDO_24
IDO_17	14	64	IDO_25
IDO_18	15	65	IDO_26
IDO_19	16	66	IDO_27
IDO_20	17	67	IDO_28
IDO_21	18	68	IDO_29
IDO_22	19	69	IDO_30
IDO_23	20	70	IDO_31
VDD3	21	71	VDD4
IGND	22	72	IGND
IGND	23	73	IGND
IGND	24	74	IGND
N/C	25	75	N/C
IDO_32	26	76	IDO_40
IDO_33	27	77	IDO_41
IDO_34	28	78	IDO_42
IDO_35	29	79	IDO_43
IDO_36	30	80	IDO_44
IDO_37	31	81	IDO_45
IDO_38	32	82	IDO_46
IDO_39	33	83	IDO_47
VDD5	34	84	VDD6
IGND	35	85	IGND
IGND	36	86	IGND
IGND	37	87	IGND
IDO_48	38	88	IDO_56
IDO_49	39	89	IDO_57
IDO_50	40	90	IDO_58
IDO_51	41	91	IDO_59
IDO_52	42	92	IDO_60
IDO_53	43	93	IDO_61
IDO_54	44	94	IDO_62
IDO_55	45	95	IDO_63
VDD7	46	96	VDD8
IGND	47	97	IGND
IGND	48	98	IGND
IGND	49	99	IGND
+5Vout	50	100	+5Vout