

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301360054](#)
Status: **Active**
Overview: [Outlet Boxes](#)
Description: Super-Safeway Multi-Tap (3) Non-NEMA 20A/125V/250V Outlet Box with Buss Bars, 7.62m (25.0') Cord Length, 12/3 SOW Cord, Non-NEMA 20A/125V/250V Plug

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Power Distribution
Series [130136](#)
Enclosure Rating N/A
GFCI Reset N/A
Mounting Style Portable
Open Neutral Relay N/A
Overview [Outlet Boxes](#)
Product Name Super-Safeway
Receptacle Type Triple
Type Multi-Tap and Strip Cordset
UPC 78678875657

Physical

Cord Diameter 15.24mm (.600")
Cord Grip Body Size Double C-Clamp
Cord Length 7.62m (25.0')
Feed-Thru No
Flip Lid No
Material - Housing Rubber
Number of Receptacles 3
Packaging Type Carton

Electrical

Cord Type 12/3 SOOW
Current - Maximum per Contact 20.0A
GFCI No
Ground Continuity Monitor No
NEMA Configuration Non-NEMA
Voltage - Maximum 120V

Material Info

Engineering Number 32708A123



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130136](#) Series