

Right Angle Panel DIP Switches

Features

Optimized Mechanical Features

- Designed for panel applications
Saves cost of right angle socket
- Multiple circuit configurations available
- Standard 2.54mm (.100") x 2.54mm (.100") centers, uses minimum PCB real estate
- Sealed version optional: assures contaminant-free switch operation after wave soldering and cleaning
- Available with low profile, standard, or extended actuators for SPST circuitry

Optimized Contact System

- Contact wiping action on make and break
- Integral terminal and contact locked into high temperature plastic base
- Electrostatic discharge shield rated to 22 KV

Materials

- Series 206RA, gold plated contacts for long-term contact corrosion resistance
- Series 208RA, tin plated contacts
- UL 94V-0 plastics
- RoHS compliant



Series 206RA – Premium Gold Plated Contacts
Series 208RA – Economical Tin Plated Contacts

Electrical and Mechanical Specifications

Switch Function

SPST - 2 through 10 and 12 positions
SPDT&DPST- 1 through 6 positions
DPDT&4PST - 1 through 3 positions
3PST - 1 through 4 positions

Switch Contact Resistance

Switch Series	Initial, max.	End of life , max.
206RA	50 milliohms	100 milliohms
208RA	100 milliohms	500 milliohms

Insulation Resistance

1,000 megohms minimum between insulated terminals

Dielectric Strength

500 VAC for 1 minute between adjacent switches

Nonswitching Rating

100 mA or 50 VDC maximum

Switch Capacitance

5.0 pF maximum between adjacent closed switches

Operating Temperature

-55°C to +85°C

Actuation Life

Series 206RA: 10,000 cycles switching 50 mA @ 24 VDC
Series 208RA: 2,000 cycles switching 50 mA @ 24 VDC

Allowable Solder Time

Wave soldering up to 5 seconds at 260°C

Vibration

Per MIL-STD-202F, method 204D, condition B
(.06" or 15 G's between 10 HZ to 2K HZ)
with no contact inconsistencies greater than 1 microsecond

Shock

Per MIL-STD-202F, method 213B, condition A
(50 G's) with no contact inconsistencies greater than 1 microsecond

Sealing

Bottom epoxy seal optional
Top tape seal optional

Marking

Special side or top marking available-consult CTS

Packaging

Standard : Anti-Static tube packaging



Standard Part # _____