




Product Data Sheet


Part No. PB-2418 Non-Washable Type

PB-2418



φ 24.0 × H18.0

DIMENSIONS



PB-2418-1: Non Epoxy Potting Material
PB-2418-2: Epoxy Potting Material

Type	Unit	PB-2418-1
Rated Voltage	(VDC)	12
Operating Voltage	(VDC)	3~20
Current Consumption	(mA)	< or =8
Sound Output (Min)	(dB)	> or = 90
Resonant Frequency	(Hz)	3700±500
Operating Temp	(C)	-20~+60
Storage Temp	(C)	-30~+70
Weight	(g)	5
Dimension	mm	24 x H18
*Value applying at rated voltage		
*distance for measurement 30cm		

Type	Unit	PB-2418-2
Rated Voltage	(VDC)	12
Operating Voltage	(VDC)	3~20
Current Consumption	(mA)	< or =8
Sound Output (Min)	(dB)	> or = 90
Resonant Frequency	(Hz)	3700±500
Operating Temp	(C)	-20~+60
Storage Temp	(C)	-30~+70
Weight	(g)	5
Dimension	mm	24 x H18
*Value applying at rated voltage		
*distance for measurement 30cm		