

 Search This Product Catalog

By Keyword

Go

[Product Catalog for Manufacturing & Industry](#) > [Bundling and Reinforcing Products](#) > [Scotch® Filament Tape 8915](#) >

Scotch® Filament Tape 8915, 768 mm X 55 m, 4 per case

 [Printer-friendly format](#)

High performance. Polypropylene backing reinforced with glass filaments to hold appliance components during manufacturing and shipping. Typical 170 lb/inch width tensile strength with clean removal adhesive.

3M Id : CT-0607-6715-0

Additional Information

Learn More . . .

[Packaging Data](#)

Stiff, heavy polypropylene backing is easy to handle and dispense. Provides excellent resistance to nicks, abrasion, moisture and scuffing. Specially formulated rubber resin adhesive bonds with high initial adhesion. Resists stains on most surfaces. Applications:- Extensive use in the appliance industry to hold doors and interior parts stationary during handling and shipping. Typical Physical [Full Text . . .](#)

Characteristics

Adhesion to Steel oz/in (N/100 mm)	65 (71)
Adhesive Material	Synthetic Rubber Resin
Backed	Yes
Backing Material	Polypropylene Film
Color	Clear
Core Size	3 Inch
Elongation	3 Percent
Product Form	Roll
Roll Length	55 Linear Metre
Tape Construction	Single Coat
Tape Type	Filament
Tensile Strength lb/in (N/100 mm)	170 (2980)
Thickness	6 Milli-inch (mil)