

LABFACILITY


TEMPERATURE & PROCESS TECHNOLOGY

Glassfibre Exposed Welded Tip Thermocouples with Plug



Types K or J with 're-wireable' miniature flat pin plug

- ◆ Thermocouple types K & J
- ◆ Fast response, welded exposed junction
- ◆ 2 or 4 metre long glassfibre insulated flat pair cable
- ◆ Good temperature resistance (not suitable in fluids)
- ◆ 1/0.315mm conductors
- ◆ 'Re-Wireable' miniature flat pin plug
- ◆ Temperature range -50°C to $+350^{\circ}\text{C}$ (short periods up to 400°C)
- ◆ Tolerance to IEC 584 Class 2
- ◆ Colour code to IEC 584-3
- ◆ Ideal for test & development applications



T/C Type	Length	+Positive tail wire	-Negative tail wire	Manufacturing Part Number	Farnell order code
'J'	4 metres	Black	White	Z3-J-F/G-1/0.315-4.0-MP	163-3493
'K'	4 metres	Green	White	Z3-K-F/G-1/0.315-4.0-MP	163-3494
'K'	2 metres	Green	White	Z3-K-F/G-1/0.315-2.0-MP	410-0773

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com