


10		9		8		7		6		5		4		3		2		19119			
LOOSE PIECE		TAPE MOUNTED		DIMENSIONS										FINISH							
MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	S ±.005	W MAX	C MIN	ID MIN	MWID	B REF	L MAX	H REF	INSULATION COLOR	F							
191190004	A-215-06X	191190005	A-215-06XT	6	.146/3.71	.301/7.6	.207/5.3	.054/1.37	.145/3.68	.450/11.43	.836/21.23	.08/2.0	RED								
191190007	A-215-08X	191190008	A-215-08XT	8	.173/4.39	.301/7.6	.207/5.3	.054/1.37	.145/3.68	.450/11.43	.836/21.23	.08/2.0	RED								
191190010	A-215-10X	191190051	A-215-10XT	10	.198/5.03	.301/7.6	.207/5.3	.054/1.37	.145/3.68	.450/11.43	.836/21.23	.08/2.0	RED								
191190080	B-216-06X	191190027	B-216-06XT	6	.146/3.71	.301/7.6	.209/5.3	.081/2.06	.175/4.45	.450/11.43	.850/21.59	.08/2.0	BLUE								
191190029	B-216-08X	191190030	B-216-08XT	8	.173/4.39	.301/7.6	.209/5.3	.081/2.06	.175/4.45	.450/11.43	.850/21.59	.08/2.0	BLUE								
191190032	B-216-10X	191190033	B-216-10XT	10	.198/5.03	.301/7.6	.209/5.3	.081/2.06	.175/4.45	.450/11.43	.850/21.59	.08/2.0	BLUE								



- NOTES:
- 1. MATERIAL: COPPER .031/.79 THICK
 - 2. PLATING: ELECTRO-TIN
 - 3. MWID = MAXIMUM WIRE INSULATION DIAMETER
 - 4. PART IS RoHS COMPLIANT

STANDARDIZE EC NO: ETC2008-0012 DRAWN: RSTONE 2007/11/26 CHKD: JMACNEIL 2007/11/26 APPR: JMACNEIL 2007/12/05 A	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION
			mm	INCH	DRAWN BY	DATE	TITLE FLANGED SPADE TERMINAL, INSULKRIMP -200 SERIES, LONG BARREL		
			4 PLACES ± ---	± ---	K0	1984/10/25			
			3 PLACES ± ---	± .005	CHECKED BY	DATE			
			2 PLACES ± 0.13	± .01	GZ	1984/11/09			
1 PLACE ± 0.25	± ---	APPROVED BY		DATE	 MOLEX INCORPORATED				
ANGULAR ±1/2°		MATERIAL NO.		DOCUMENT NO.			SHEET NO.		
REV	A		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-19119-003		1 OF 1
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[19119-0080](#) [19119-0032](#)