

# PANEL MOUNT INDICATOR, NON-RELAMPABLE

## NEON TECHNOLOGY

MOUNTING HOLE, Ø 0.500"

| PART NO.                       | LENS COLOR | VOLTAGE    | CURRENT [mA] | RATED LIFE HOURS |
|--------------------------------|------------|------------|--------------|------------------|
| <b>NEON 115VAC SERIES</b>      |            |            |              |                  |
| WL-1050QC1                     | RED        | 105-125VAC | 1.5mA        | 25,000           |
| WL-1050QC2                     | CLEAR      | 105-125VAC | 1.5mA        | 25,000           |
| WL-1050QC3                     | AMBER      | 105-125VAC | 1.5mA        | 25,000           |
| WL-1050QC4                     | WHITE      | 105-125VAC | 1.5mA        | 25,000           |
| WL-1052QC5                     | GREEN      | 105-125VAC | 1.5mA        | 25,000           |
| <b>NEON 230VAC SERIES</b>      |            |            |              |                  |
| WL-1051QC1                     | RED        | 208-250VAC | 1.5mA        | 25,000           |
| WL-1051QC2                     | CLEAR      | 208-250VAC | 1.5mA        | 25,000           |
| WL-1051QC3                     | AMBER      | 208-250VAC | 1.5mA        | 25,000           |
| WL-1051QC4                     | WHITE      | 208-250VAC | 1.5mA        | 25,000           |
| WL-1053QC5                     | GREEN      | 208-250VAC | 1.5mA        | 25,000           |
| <b>INCANDESCENT 12V SERIES</b> |            |            |              |                  |
| WL-1090QC1-12V                 | RED        | 12V-14V    | 80mA         | 25,000           |
| WL-1090QC3-12V                 | AMBER      | 12V-14V    | 80mA         | 25,000           |
| WL-1090QC4-12V                 | WHITE      | 12V-14V    | 80mA         | 25,000           |
| WL-1090QC5-12V                 | GREEN      | 12V-14V    | 80mA         | 25,000           |
| <b>INCANDESCENT 28V SERIES</b> |            |            |              |                  |
| WL-1090QC1-28V                 | RED        | 24V-28V    | 40mA         | 25,000           |
| WL-1090QC3-28V                 | AMBER      | 24V-28V    | 40mA         | 25,000           |
| WL-1090QC4-28V                 | WHITE      | 24V-28V    | 40mA         | 25,000           |
| WL-1090QC5-28V                 | GREEN      | 24V-28V    | 40mA         | 25,000           |

## NOTES

1. Recommended panel thickness  
0.030" to 0.090"
2. .187" terminals are standard
3. Storage temperature  
 $T_{STG}$ : -25°C - +80°C
4. Ambient temperature  
 $T_A$ : -20°C - +60°C
5. AC operation only for neon type
6. AC/DC operation for incandescent type
7. Voltage tolerance  
 $V_{OP}$ :  $\pm 10\%$
8. Body material  
Nylon, white
9. Lens material  
Polycarbonate
10. Bezel material  
Stainless steel
11. .250" terminals available upon request


## CERTIFICATIONS

UL (E340667), RoHS



**RoHS**  
COMPLIANT

## DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in inches



## OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

