

C57 UK Dual Cord 30VA Transformer Series

Features

- 230 VAC Input
- UK Dual Cord Style
- Rated for Continuous Duty
- AC outputs up to 30VA
- Meets Safety Agency Requirements
- Complies with EMI/RFI Regulations
- CE Compliant
- Impact Resistant Polycarbonate Enclosure
- Private Label Marking Available
- 1 Year Warranty
- Modified and Custom Designs Also Available
- Manufactured in China

Ault Model	Rated Output Volts AC	Maximum Current-Amps	Maximum VA
C57-065000-K000G	6	5.00	30.0
C57-074286-K000G	7	4.29	30.0
C57-083750-K000G	8	3.75	30.0
C57-093333-K000G	9	3.33	30.0
C57-103000-K000G	10	3.00	30.0
C57-112727-K000G	11	2.73	30.0
C57-122500-K000G	12	2.50	30.0
C57-142143-K000G	14	2.14	30.0
C57-152000-K000G	15	2.00	30.0
C57-161875-K000G	16	1.88	30.0
C57-181666-K000G	18	1.66	30.0
C57-201500-K000G	20	1.50	30.0
C57-221364-K000G	22	1.36	30.0
C57-241250-K000G	24	1.25	30.0

*To be assigned at time of order placement

Input	
• Voltage	230 VAC
• Line Frequency	50 Hz
• Connector	UK Dual Cord, No Ground

Electrical	
• Topology	Step Down AC/AC Transformer
• Dielectric Withstand	3000 VAC primary-secondary 1500 VAC primary-core 500 VAC secondary-core
• Protection	Current, Thermal or Energy Limiting
• EMI	Complies with EMC Directives
• CE	CE Compliant

Safety Approvals	
• Safety Agencies	TUV EN60950

Environmental	
• Operating Temperature	0° to 40° C with no derating
• Storage Temperature	-30° to +85° C
• Relative Humidity	5% to 95% non-condensing
• Altitude	0-10,000 feet
• Cooling	Convectional - non vented case

Mechanical	
• Case Dimensions	A57 - UK Dual Cord 3.5 L x 2.6 W x 2.2 H (in) 89 L x 67 W x 55 H (mm)
• Case Material	Black 94 V1 Polycarbonate
• Weight	30 ounces, 850 grams, (excluding cord)
• Cord and Connector	6 ft., 2 Conductor, 18-20 AWG Ault #3 Connector Other Connectors Available

ONE YEAR WARRANTY

