




## Wiha SoftFinish® Handle - Standard Series

**NEW**  
From Wiha


[SHOP](#)

### 302 91 Set 6 Pcs. Slotted, Phillips & Square Cushion Grip Drivers

| Item No. | Slotted | mm  | mm  | Phillips | Size | mm  | Square | Size | mm  |
|----------|---------|-----|-----|----------|------|-----|--------|------|-----|
| 302 91   | 302 11  | 4.5 | 125 | 311 10   | 1    | 80  | 358 01 | 1    | 100 |
|          | 302 25  | 6.5 | 150 | 311 15   | 2    | 100 | 358 02 | 2    | 150 |
| lbs.     | 1.00    |     |     |          |      |     |        |      |     |

**NEW**  
From Wiha


[SHOP](#)

### 302 90 Set 10 Pcs. Slotted, Phillips & Square Cushion Grip Drivers

| Item No. | Slotted | mm  | mm  | Phillips | Size | mm  | Square | Size | mm  |
|----------|---------|-----|-----|----------|------|-----|--------|------|-----|
| 302 90   | 302 05  | 3.0 | 100 | 311 05   | 0    | 60  | 358 01 | 1    | 100 |
|          | 302 10  | 3.5 | 125 | 311 10   | 1    | 80  | 358 02 | 2    | 150 |
| lbs.     | 302 11  | 4.5 | 125 | 311 15   | 2    | 100 | 358 03 | 3    | 150 |
| 1.40     | 302 25  | 6.5 | 150 |          |      |     |        |      |     |


[SHOP](#)

### 302 99 Set 20 Pcs. Slotted, Phillips, TORX®, Square & Pozidriv®

| Item                                                                               |  |      |     |  |      |     |  |      |     |
|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|------|-----|-------------------------------------------------------------------------------------|------|-----|-------------------------------------------------------------------------------------|------|-----|
| No.                                                                                | Slotted                                                                             | mm   | mm  | Phillips                                                                            | Size | mm  | TORX®                                                                               | Size | mm  |
| 302 99                                                                             | 302 05                                                                              | 3.0  | 100 | 311 05                                                                              | 0    | 60  | 362 66                                                                              | T6   | 60  |
|  | 302 15                                                                              | 4.0  | 100 | 311 10                                                                              | 1    | 80  | 362 70                                                                              | T8   | 60  |
| lbs.                                                                               | 302 20                                                                              | 5.5  | 125 | 311 15                                                                              | 2    | 100 | 362 74                                                                              | T10  | 80  |
| 3.27                                                                               | 302 25                                                                              | 6.5  | 150 |                                                                                     |      |     | 362 76                                                                              | T15  | 80  |
|                                                                                    | 302 30                                                                              | 8.0  | 175 |  |      |     | 362 78                                                                              | T20  | 100 |
|                                                                                    |  |      |     | Square                                                                              | Size | mm  | 362 80                                                                              | T25  | 100 |
|                                                                                    | Pozidriv                                                                            | Size | mm  | 358 01                                                                              | 1    | 100 | 362 84                                                                              | T30  | 115 |
|                                                                                    | 313 10                                                                              | 1    | 80  | 358 02                                                                              | 2    | 150 |                                                                                     |      |     |
|                                                                                    | 313 15                                                                              | 2    | 100 | 358 03                                                                              | 3    | 150 |                                                                                     |      |     |