



SINGLE LEVEL T1 (3mm) LEDs


PC110




PCM110




PCL110




PC120



PCM120




PCL120




Options

-SO
STAND OFF




-P
LOCATING PIN




Arrays


12PC120



13PC120



14PC120



CODE	COLOR	mA	Vf	Iv mcd
R	RED	10/30	2.0/2.8	1.7/5.6
Y	YELLOW	10/20	2.1/2.8	1.7/5.5
G	GREEN	10/30	2.1/2.8	1.7/5.6
B	BLUE	20/30	3.2/3.7	2.0/3.5

SAMPLE PART NUMBER:

PC120TX4

LED COLOR

SPECIALS

- ALL "Vf" READINGS ARE TYP/MAX
- ALL "mcd" READINGS ARE MIN/TYP
- 5V = 5 VOLT INTEGRATED RESISTOR
- LC = LOW CURRENT 2mA LEDs
- X = DENOTES BLANK LED SPACE
- CONSULT FACTORY ON PART NUMBERS FOR ARRAYS WITH NONCONSECUTIVE COLORS