



Terminal Block Headers




158-P022EHDRCH SERIES

KOBICONN

Terminal Block Headers



P.C.B. LAYOUT (REF)



Dimensions: mm (In.)

P	02P	03P	04P	05P	06P	07P	08P	09P	10P	11P	12P
U (mm)	5.08	10.16	15.24	20.32	25.40	30.48	35.55	40.64	45.72	50.80	55.88
V (mm)	11.38	16.44	21.52	26.6	31.68	36.76	41.84	46.92	52.0	57.08	62.16

MATERIALS

Solder Pin:	Tin plated copper
Housing:	PA66 green

ELECTRICAL SPECIFICATIONS

Rating:	300V/15A 5mm pitch
Insulation Resistance:	500MΩ or more @ 500VDC
Insulation Withstand Voltage:	1500VAC min.
Using Temperature Range:	1A @ 10VDC

Date Last Revised: 10/19/05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300778

158-P022EHDRCH SERIES

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[158-P102EHDRCH](#) [158-P022EHDRCH](#)