

[illegible]

Poles	Tolerance	
	DIM L	DIM P
2p-4p	±0.20	±0.20
5p-8p	±0.30	±0.25
9p-12p	±0.40	±0.30

N=Number of poles

L	Nx10.0-2.5
P	(N-1)x10.0

DIMENSION

Electrical cULus
Voltage rating: 300VAC
Current rating: 20A
Wire range:
Solid wire(AWG): 12-22
Stranded wire(AWG): 12-22
Torque(lb-in): 2.4
Screw: M2.5
Wire strip length: 10-11mm
Withstanding Voltage: 1.6kV
Operating temperature: -40°C to +115°C
Soldering temperature: 250°C±10°C/5 Sec
Safety Approval: us