


FK-MC 0,5/ 2-ST-2,5

Order No.: 1881325

The figure shows a 10-position version of the product



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1881325>

Plug component, Nominal current: 4 A, Nom. voltage: 100 V, Pitch:
2.5 mm, Number of positions: 2, Connection type: Spring-cage conn.,
Color: green

Commercial data

EAN	4017918156572
Pack	50 pcs.
Customs tariff	85366990
Weight/Piece	0.00147 KG
Catalog page information	Page 136 (CC-2009)

Product notes

WEEE/RoHS-compliant since:
01/01/2003



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Dimensions / positions

Pitch	2.5 mm
Dimension a	2.5 mm
Number of positions	2

Technical data

Insulating material group	I
Rated surge voltage (III/3)	1.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/2)	160 V
Rated voltage (II/2)	320 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	4 A
Nominal voltage U_N	100 V
Nominal cross section	0.5 mm ²
Maximum load current	4 A (with 0.5 mm ² conductor cross section)
Insulating material	PA
Inflammability class acc. to UL 94	V0
Stripping length	8 mm

Connection data

Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	0.5 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	0.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	0.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	20

Certificates / Approvals



Certification

CB, CUL, GOST, UL, VDE-PZI

CUL

Nominal voltage U_N	125 V
Nominal current I_N	4 A

AWG/kcmil	28-20
-----------	-------

UL

Nominal voltage U_N	125 V
Nominal current I_N	4 A
AWG/kcmil	28-20

Accessories

Item	Designation	Description
Marking		
0804853	SK 2,54/2,8:FORTL.ZAHLEN	Marker card, printed horizontally, self-adhesive, 10-section marker strip, 14 identical decades marked 1-10, 11-20 etc. up to 91-100, sufficient for 140 terminal blocks

Tools



1205202	SZS 0,4X2,0	Screwdriver, bladed, matches all screw terminal blocks up to 1.5 mm ² connection cross section, blade width: 2.5 mm, without approvals
---------	-------------	---

Additional products


Item	Designation	Description
General		
1881448	MC 0,5/ 2-G-2,5	Header, Nominal current: 4 A, Nom. voltage: 80 V, Pitch: 2.5 mm, Number of positions: 2, Color: green, Assembly: Soldering
1894804	MCD 0,5/ 2-G1-2,5	Header, Nominal current: 4 A, Nom. voltage: 80 V, Pitch: 2.5 mm, Number of positions: 2, Color: green, Assembly: Soldering
1894914	MCDV 0,5/ 2-G1-2,5	Header, Nominal current: 4 A, Nom. voltage: 80 V, Pitch: 2.5 mm, Number of positions: 2, Color: green, Assembly: Soldering
1881558	MCV 0,5/ 2-G-2,5	Header, Nominal current: 4 A, Nom. voltage: 80 V, Pitch: 2.5 mm, Number of positions: 2, Color: green, Assembly: Soldering

Diagrams/Drawings

Diagram



Dimensioned drawing



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;