

PANEL MOUNT INDICATOR, NON-RELAMPABLE

NEON AND INCANDESCENT TECHNOLOGY

MOUNTING HOLE, Ø 0.500"

PART NO.	LENS COLOR	VOLTAGE	CURRENT [mA]	RATED LIFE HOURS
NEON 115VAC SERIES				
WL-1050C1	RED	105-125VAC	1.5mA	25,000
WL-1050C2	CLEAR	105-125VAC	1.5mA	25,000
WL-1050C3	AMBER	105-125VAC	1.5mA	25,000
WL-1050C4	WHITE	105-125VAC	1.5mA	25,000
WL-1052C5	GREEN	105-125VAC	1.5mA	25,000
NEON 230VAC SERIES				
WL-1051C1	RED	208-250VAC	1.5mA	25,000
WL-1051C2	CLEAR	208-250VAC	1.5mA	25,000
WL-1051C3	AMBER	208-250VAC	1.5mA	25,000
WL-1051C4	WHITE	208-250VAC	1.5mA	25,000
WL-1053C5	GREEN	208-250VAC	1.5mA	25,000
INCANDESCENT 12V SERIES				
WL-1090C1-12V	RED	12V-14V	80mA	25,000
WL-1090C3-12V	AMBER	12V-14V	80mA	25,000
WL-1090C4-12V	WHITE	12V-14V	80mA	25,000
WL-1090C5-12V	GREEN	12V-14V	80mA	25,000
INCANDESCENT 28V SERIES				
WL-1090C1-28V	RED	24V-28V	40mA	25,000
WL-1090C3-28V	AMBER	24V-28V	40mA	25,000
WL-1090C4-28V	WHITE	24V-28V	40mA	25,000
WL-1090C5-28V	GREEN	24V-28V	40mA	25,000

NOTES

1. Recommended panel thickness
0.030" to 0.090"
2. 6" leads with 1/2" strip are standard
3. Storage temperature
TSTG: -25°C - +80°C
4. Ambient temperature
TA: -20°C - +60°C
5. AC operation only for neon type
6. AC/DC operation for incandescent type
7. Voltage tolerance
VOP: ± 10%
8. Body Material
Nylon, white
9. Lens Material
Polycarbonate
10. Bezel Material
Stainless steel
11. Wire Gauge
18 AWG
12. Wire Strip
1/2"


CERTIFICATIONS

UL (E340667), RoHS



RoHS
COMPLIANT

DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in inches



OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

