

Polypropylene Rods And Sheets



- High flexural fatigue resistance
- Good impact strength
- Resists steam cleaning
- Natural white colour
- Excellent electrical properties
- Continuous working temperature 80°C (Max. 100°C)
- Excellent chemical resistance (pH4-11)
- Limited UV resistance
- All dimensions are approximate

Specific gravity	1.43	Relative permittivity at 1kHz	2.25
Flexural modulus of elasticity	1150 N/mm ²	Volume resistivity	10 ¹⁵ cm
Tensile strength at yield	27 N/mm ²	Surface resistivity	1011 to 1015Ω
Elongation at yield	15%		

Rod 1 Metre Length

Diameter (mm)	Quantity Per Lot	Order Code	Price Each
20	3	521-309	
30	2	521-310	
40	1	521-322	

Sheet

493767

Sheet Size (mm)	Quantity Per Lot	Order Code	Price Each
3 x 995 x 495	3	521-334	
4.5 x 995 x 495	2	521-346	
6 x 995 x 495	2	521-358	
9 x 995 x 495	1	521-360	
10 x 995 x 495	1	521-371	
15 x 995 x 495	1	521-383	