




Voice/Data Cable Markers

Ideal for marking data cabling, this cable marker's protected printing offers superior abrasion resistance and resistance to dirt, oils, solvents and water. Marker features a clear, non-printed area which wraps around and overlaminates the printed text. Printer automatically "multiple repeats" your text in the white print area. B-427 Vinyl Self Laminating material.

- Resistant to abrasion, water, oil and solvents
- UL recognized
- Temp range -94°F to 158°F (-70C to 70C)

Diagram D



Sized to Fit	Diagram	Part Number	# per Cartridge	Dimensions (in.)			Dimensions (mm)			Color
2 pair Fiber/Coaxial, Single/Multi Mode	D	XSL-19-427	250	1.000	1.000	0.375	25.40mm	25.40mm	9.53mm	BK on WT
CAT-5, 4 pair UTP Copper	D	XSL-102-427	250	0.500	1.250	0.375	12.70mm	31.75mm	9.53mm	BK on WT
CAT-5, 4 pair UTP Copper, Fiber, Coaxial	D	XSL-103-427	250	1.000	1.250	0.500	25.40mm	31.75mm	12.70mm	BK on WT
CAT-5, 4 pair UTP Copper	D	XSL-115-427	250	1.500	1.250	0.500	38.10mm	31.75mm	12.70mm	BK on WT
CAT-5, 4 pair UTP Copper	D	XSL-29-427	500	0.500	1.500	0.500	12.70mm	38.10mm	12.70mm	BK on WT
CAT-5, 4 pair UTP Copper	D	XSL-30-427	250	0.750	1.500	0.500	19.05mm	38.10mm	12.70mm	BK on WT
CAT-5, 4 pair UTP Copper, Fiber, Coaxial	D	XSL-31-427	250	1.000	1.500	0.500	25.40mm	38.10mm	12.70mm	BK on WT
CAT-5, 4 pair UTP Copper, Fiber, Coaxial	D	XSL-31-427-YL-BK	250	1.000	1.500	0.500	25.40mm	38.10mm	12.70mm	BK on YL
CAT-5, 4 pair UTP Copper, Fiber, Coaxial	D	XSL-32-427	250	1.500	1.500	0.500	38.10mm	38.10mm	12.70mm	BK on WT
25 pair Copper, 4-12 pair Fiber, Coaxial	D	XSL-21-427	100	1.000	2.500	0.750	25.40mm	63.50mm	19.05mm	BK on WT
25 pair Copper, 4-12 pair Fiber, Coaxial	D	XSL-21-427-YL-BK	100	1.000	2.500	0.750	25.40mm	63.50mm	19.05mm	BK on YL
25 pair Copper, 4-12 pair Fiber, Coaxial	D	XSL-116-427	100	1.500	2.500	0.750	38.10mm	63.50mm	19.05mm	BK on WT
50 pair Copper, 24 pair Fiber, Backbone	D	XSL-23-427	100	1.000	4.000	1.000	25.40mm	101.60mm	25.40mm	BK on WT
50 pair Copper, 24 pair Fiber, Backbone	D	XSL-23-427-YL-BK	100	1.000	4.000	1.000	25.40mm	101.60mm	25.40mm	BK on YL
50 pair Copper, 24 pair Fiber, Backbone	D	XSL-33-427	100	1.500	4.000	1.000	38.10mm	101.60mm	25.40mm	BK on WT
100 pair Copper, 36 pair Fiber, Backbone	D	XSL-34-427	50	1.500	6.000	1.500	38.10mm	152.40mm	38.10mm	BK on WT



Voice/Data Patch Panel, Outlet & Faceplate Markers

B-422 Gloss Polyester

- Permanent adhesive for smoother surfaces
- Temp Range -40°F to 212°F (-40C to 82C)
- UL Recognized

Diagram A





Diagram B



Application	Diagram	Part Number	Labels per Cartridge	Dimensions (in.)		Dimensions (mm)		Color
Label Each Port	A	X-7-422	350	0.500	0.500	12.70mm	12.70mm	BK on WT
Label Punch Blocks or Multiple Ports on Cont. Tape	B	XC-375-422	1 roll (cont.)	30 ft.	0.375	9.14mm	9.53mm	BK on WT
Label Punch Blocks or Multiple Ports on Cont. Tape	B	XC-475-422	1 roll (cont.)	30 ft.	0.475	9.14mm	12.07mm	BK on WT
Label Faceplate	A	X-17-422	500	1.000	0.500	25.40mm	12.70mm	BK on WT
Label Faceplate	A	X-29-422	500	1.500	0.500	38.10mm	12.70mm	BK on WT



Voice/Data I.D. for Racks, Bays, Frames, Public Network & Data Centers

B-422 Gloss Polyester

- Permanent adhesive
- Temp Range -40°F to 212°F (-40C to 100C)
- UL Recognized

B-483 Ultra-Aggressive Polyester

- Permanent adhesive for textured/powder-coated surfaces
- Temp Range -40°F to 248°F (-40C to 120C)
- UL Recognized

B-595 Indoor/Outdoor Vinyl

- Permanent adhesive, good for rough surfaces
- Wide range of colors
- Temp Range -40°F to 248°F (-40C to 82C)

Diagram A





Diagram B



Material Notes	Diagram	Part Number	Labels per Cartridge	Dimensions (in.)		Dimensions (mm)		Color
Ultra Polyester for textured surfaces	A	X-17-483	500	1.000	0.500	25.40mm	12.70mm	BK on WT
Ultra Polyester for textured surfaces	A	X-61-483	100	2.000	0.500	50.80mm	12.70mm	BK on WT
Ultra Polyester for textured surfaces	A	X-20-483	100	2.000	1.000	50.80mm	25.40mm	BK on WT
Gloss Polyester	A	X-17-422	500	1.000	0.500	25.40mm	12.70mm	BK on WT
Gloss Polyester	A	X-29-422	500	1.500	0.500	38.10mm	12.70mm	BK on WT
Gloss Polyester	A	X-30-422	250	1.500	0.750	38.10mm	19.05mm	BK on WT
Gloss Polyester	A	X-19-422	250	1.000	1.000	25.40mm	25.40mm	BK on WT
Gloss Polyester	B	XC-1000-422	1 roll (cont.)	30 ft.	1.000	9.14mm	25.40mm	BK on WT
Indoor/Outdoor Vinyl (colored supplies)	B	XC-500-595-YL-BK	1 roll (cont.)	30 ft.	0.500	9.14mm	12.70mm	BK on YL*
Indoor/Outdoor Vinyl (colored supplies)	B	XC-1000-595-YL-BK	1 roll (cont.)	30 ft.	1.000	9.14mm	25.40mm	BK on YL*
Indoor/Outdoor Vinyl (colored supplies)	B	XC-1500-595-YL-BK	1 roll (cont.)	30 ft.	1.500	9.14mm	38.10mm	BK on YL*

*also available in Red, Orange, Green, Blue, White, and Clear