


D


C

B

A



- 1 PHOSPHOR BRONZE PER ASTM-B-139
 - 2 CARBON STEEL
 - 3 BRASS PER MIL-C-50
 - 4 BRASS PER QQ-B-626
 - 5 SILICONE RUBBER PER ZZ-R-765
 - 6 POLYMETHYLPENTENE: GENERAL PURPOSE
 - 7 ZINC DIE CAST PER QQ-Z-363
 - 8 GOLD PLATING PER MIL-G-45204
0.38µm [0.000015] MIN THICKNESS
 - 9 NICKEL PLATING PER QQ-N-290
2.54µm [0.000100] MIN THICKNESS
 - 10 NICKEL PLATING PER QQ-N-290
3.81µm [0.000150] MIN THICKNESS
 - 11 NICKEL PLATING PER QQ-N-290
4.45µm [0.000175] MIN THICKNESS
12. USE INSTRUCTION SHEET 408-6996



RECOMMENDED STRIP LENGTH

OBSOLETE	RG-58B/U	4.47 [0.176]	414265-7
OBSOLETE	RG-59/U	5.49 [0.216]	414265-6
OBSOLETE	BELDEN 8281	6.91 [0.272]	414265-5
OBSOLETE	BELDEN 88241	4.62 [0.182]	414265-4
	RG-59/U	5.49 [0.216]	414265-3
OBSOLETE	BELDEN 88240	4.06 [0.160]	414265-2
	RG-58B/U	4.47 [0.176]	414265-1
CABLE		A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

M.E. COWHER

23JAN92

CHK

M. PHILLIPS

4-21-92

APVD

-

-

DIMENSIONS:

mm [INCHES]

0 PLC

±

-

1 PLC

±

-

2 PLC

±

0.51 [0.020]

3 PLC

±

-

4 PLC

±

-

ANGLES

±

-

FINISH

±

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

±

-

±

0.51 [0.020]

±

-

±

-

±

-

MATERIAL

SEE NOTES

WEIGHT

-

CUSTOMER DRAWING

PRODUCT SPEC

-

APPLICATION SPEC

-

NAME

PLUG ASSEMBLY, 50 OHM, TWIST-ON, BNC

SIZE

A2

CAGE CODE

00779

DRAWING NO

414265

RESTRICTED TO

-

SCALE

4:1

SHEET

1 of 1

REV

K