

C-172866

NUMBER





METRIC

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST

REV. 10/82



回路番号
(奇数番号を表示)
CIRCUIT No. (ODD No. ONLY)
1, 3, 5, 7, 9, 11, 13, 15, 17, 19, 21, 23, 25
(1, 3, 5, 7, 9, 11, 13, 15, 17, 19, 21, 23, 25)

NOTES: Δ MATERIAL

HOUSING: PBT (UL 94V-0) BLACK

CONTACT: Phos-Bz (TIN PLATE), 0.3THK.

2. MATING SPR. HDR. ASS'Y

Vertical Type: 172870 (WITH POLARIZATION)
(Tin Plated) 173052 (WITHOUT POLARIZATION)

注: 1. 材料

ハウジング

PBT (UL 94V-0) 黒色


コンタクト

: リン青銅 (錫めっき) 板厚 0.3t

2. 適用スプリング ヘッダー アッセンブリ型番
垂直型 (錫めっき)

172870 (基板取付極性有)

173052 (基板取付極性無)



68.54	60.96	24	50	5-172866-0
55.84	48.26	19	40	4- -0
48.22	40.64	16	34	3- -4
45.68	38.10	15	32	3- -2
43.14	35.56	14	30	3- -0
40.60	33.02	13	28	2- -8
38.06	30.48	12	26	2- -6
35.52	27.94	11	24	2- -4
32.98	25.40	10	22	2- -2
30.44	22.86	9	20	2- -0
27.90	20.32	8	18	1-172866-8

C	D	E	Pos.	PART No.
DEMENSION				

D	REVISED (FJ00-0624-02)	T.T	I.E	3/22/02
C	REVISED (J-9163)	T.S	A	1/10/95
B	REVISED (J-9045)	T.S	A	2/19/95
A1	REVISED (J85-8319)	T.S	A	
A	REVISED (J84-8000)	E.Y.N.	O	
O	RELEASED (J84-7631)	E.Y.N.	O	
LTR	REVISION RECORD	OR	CHK	DATE

WIRE RANGE AWG #28, 26, 24	INSULATION DIA 0.88-1.56 mm	NAME
MATERIAL Δ SEE NOTES	FINISH Δ SEE NOTES	
DR. 5/7/84 E. YOSHIDA	DE. 5/7/84 E. YOSHIDA	
CHK. 5/8/84 N. ONOUE	APP. 5/8/84 A. TOMITA	

tyco
ElectronicsTyco Electronics Corporation
Kawasaki, JapanMT RECE ASS'Y - TIN
AMP ULTREX 2.54 DCL ROW CONN.

GENERAL TOLERANCE	SIZE	LOC	NUMBER
0-10 : ±0.2 10-30 : ±0.25 30-100 : ±0.3 ANGLES : ±3°	A3	J	C-172866
SCALE 5-1	REV. D	SHEET 1 OF 1	

CUSTOMER DRAWING