



710-106/107/370 and 710-108/109/371 Metal "Y" and "T" Transitions for Series 72 & 74 Tubing and Series 75 Conduit

Metal "T" & "Y" Transitions for use with Transition Fittings



How To Order

Product Series

710

- 106

Finish (Table II)

M

"B" End Dash No.

A24

B08

C16

Y Transition Material

106 = Aluminum

107 = Brass

370 = Stainless Steel

T Transition Material

108 = Aluminum

109 = Brass

371 = Stainless Steel

"A" End Dash No.

"C" End Dash No.





Table II: Finish

Sym	Finish
B	Olive Drab over Cadmium Plate
J	Gold Iridite over Cadmium Plate over Nickel
M	Electroless Nickel
N	Olive Drab over Cadmium Plate over Nickel
NC	Zinc Cobalt, Olive Drab
NF	Olive Drab over Cadmium Plate over Electroless Nickel (1000 Hour salt Spray)
T	Bright Dip Cadmium over Nickel
Z1	Passivate

Table III: Conduit Dash No./Dimensions

Dash No.	Conduit Size (Ref)			H Thread Class 2A	D Max	E Max	F Max	G Max
	72	74	75					
06	06	06	-	7/16 - 28 UNEF	1.97 (50.0)	1.20 (30.5)	1.33 (33.8)	.81 (20.6)
08	-	-	08	1/2 - 20 UNF	1.97 (50.0)	1.20 (30.5)	1.35 (34.3)	.84 (21.3)
09	09	09	09	9/16 - 24 UNEF	2.13 (54.1)	1.30 (33.0)	1.43 (36.3)	.88 (22.4)
10	-	10	-	9/16 - 24 UNEF	2.13 (54.1)	1.30 (33.0)	1.43 (36.3)	.88 (22.4)
12	12	12	12	5/8 - 24 UNEF	2.22 (56.4)	1.34 (34.0)	1.47 (37.3)	.91 (23.1)
14	14	14	-	11/16 - 24 UNEF	2.37 (60.2)	1.49 (37.8)	1.58 (40.1)	.94 (23.9)
16	16	16	16	3/4 - 20 UNEF	2.37 (60.2)	1.49 (37.8)	1.65 (41.9)	.94 (23.9)
20	20	20	20	7/8 - 20 UNEF	2.69 (68.3)	1.70 (43.2)	1.78 (45.2)	1.03 (26.2)
24	24	24	24	1 - 20 UNEF	2.75 (69.9)	1.84 (46.7)	1.85 (47.0)	1.13 (28.7)
28	28	28	-	1 3/16 - 18 UNEF	3.06 (77.7)	2.09 (53.1)	2.09 (53.1)	1.16 (29.5)
32	32	32	32	1 5/16 - 18 UNEF	3.28 (83.3)	2.23 (56.6)	2.43 (61.7)	1.16 (29.5)
40	40	40	40	1 1/2 - 18 UNEF	3.59 (91.2)	2.50 (63.5)	2.65 (67.3)	1.28 (32.5)
48	48	48	48	1 3/4 - 18 UNS	4.23 (107.4)	2.96 (75.2)	3.15 (80.0)	1.53 (38.9)
56	-	56	56	2 - 18 UNS	5.00 (127.0)	3.50 (88.9)	3.40 (86.4)	1.69 (42.9)
64	-	64	64	2 1/4 - 16 UN	5.00 (127.0)	3.50 (88.9)	3.75 (95.3)	1.87 (47.5)
80	-	-	80	2 3/4 - 16 UN	5.70 (144.8)	4.10 (104.1)	4.25 (108.0)	2.13 (54.1)

* Consult factory for adapters using 3.000 inch (76.2) conduit

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[710-106NFA16B12C12](#) [710-108NFA40B40C40](#) [710-108NFA24B32C20](#) [710-108NFA24B16C16](#) [710-106BA32B14C32](#) [710-106NFA12B12C12](#) [710-106NFA14B14C14](#) [710-106MA32B24C32](#) [710-106NFA24B20C20](#) [710-108NFA24B32C16](#) [710-106NFA12B06C06](#) [710-106NFA14B09C14](#) [710-106NFA20B14C14](#) [710-106MA24B20C24](#) [710-108NFA16B16C24](#) [710-108NFA32B32C32](#) [710-106MA32B24C24](#) [710-106NFA24B16C16](#) [710-109MA08B16C08](#) [710-106MA24B16C20](#) [710-106NFA56B40C40](#) [710-106MA06B06C06](#) [710-108NFA16B16C16](#) [710-106MA24B24C24](#) [710-106MA24B16C24](#) [710-109NFA28B28C28](#) [710-106MA12B12C12](#) [710-106NFA20B20C20](#) [710-106MA09B09C09](#) [710-106MA20B24C20](#) [710-106MA20B16C20](#) [710-108MA16B12C12](#) [710-106MA24B24C20](#) [710-108NFA24B16C24](#) [710-106NFA08B08C08](#) [710-108NFA24B40C24](#) [710-106NFA64B16C40](#)