

Ø 171X51 mm

SUNON


Alveolate Motor

203-239 CFM




Model	P/N	Bearing	Rating Voltage (VAC)	Freq. (Hz)	Power Current (AMP)	Power Consumption (WATTS)	Speed (RPM)	Air Flow (CFM)	Static Pressure (Inch-H ₂ O)	Noise (dBA)	Weight (g)
A1175-HBL	TC.R.GN	○ BALL	115	50/60	0.22/0.23	25/27	2800/3200	203/239	0,62/0,69	51/58	908
A1175-HBT	TC.R.GN	○ BALL	115	50/60	0.22/0.23	25/27	2800/3200	203/239	0,62/0,69	51/58	908
A2175-HBL	TC.R.GN	○ SLEEVE	220-240	50/60	0.11/0.11	25/26	2800/3200	203/239	0,62/0,69	51/58	908
A2175-HBT	TC.R.GN	○ SLEEVE	220-240	50/60	0.11/0.11	25/26	2800/3200	203/239	0,62/0,69	51/58	908

Frame : Aluminum alloy



UNITS:mm



*All model could be customized on voltage or any other requirements to fit your need.

*Specifications subject to change without notice. Please Visit SUNON web site at <http://www.sunon.com> for update information.