

HS6-1L



Shrink-Kon®

HS Series Heavy-Wall Heat-Shrinkable
Tubing — Black

General

T&B Sales Drawings:	WSD-000473
Type:	Heavy-Wall Heat-Shrinkable Tubing
Shrink Ratio:	3:1
Color:	Black
T&B UPC:	78621089067
T&B Status:	M
Material:	Thermoplastic adhesive liner

Dimension Information

Cable Range:	#6 to #2 AWG
Max. Recovered I.D. (in):	0.24
Max. Recovered I.D. (mm):	6.10
Min. Expanded I.D. (in):	0.75
Min. Expanded I.D. (mm):	19.10
Nom. Recovered Wall (in):	0.12
Nom. Recovered Wall (mm):	2.40
Std. Length (in.):	8
Continuous Operating Temperature:	-55°C to 110°C
Shrink Temperature:	120°C