


REV.	DATE	ECR NO.	DESCRIPTION
NC	08/04/10	XXXXXX	INITIAL RELEASE



1. FREQUENCY RANGE: DC 0–3 GHz
2. VSWR(RETURN LOSS): 1.15, MAX.

6	SPANNER NUT	BRASS	NICKEL	1
5	INSULATOR	PTFE	NATURAL	1
4	HOUSING	BRASS	BRIGHT TIN	1
3	INSULATOR	PTFE	NATURAL	1
2	CONTACT PIN	PHOSPHOR BRONZE	GOLD	1
1	BODY	BRASS	GOLD	1
	DESCRIPTION	MATERIAL	FINISH	QTY

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	
	DRAWN	M.ZHANG	08/04/10
	CHECKED		
	ISSUED		
	SHEET	1 OF 1	
	CAD FILE	C:/CONNEX/282139-75.DWG	

Amphenol Connex				
PART DESCRIPTION 1.0/2.3 R/A BULKHEAD PCB RECEPT. JACK (75 ohm)				
PART NO. 282139-75				
DWG. NO. 282139-75.DWG		REV. NC	SIZE A	SCALE NA