





规格Specifications

额定负荷 Ratings	DC 30 V 0.1 A
初期接触电阻 Initial Contact Resistance	80 mΩ Max.
绝缘电阻 Insulation Resistance	DC 500 V 60 Sec. 100 MΩ Min.
抗电强度 Dielectric Voltage	AC 500 V (50~60HZ) 60 Sec.

操作力 Operating Force	150±50gf
负荷寿命 Operating Life With Load	10,000 次 Cycles

07	端子 TERMINAL	C2680R	6	Ag PLATED				
06	锁针 LOCK HOOK	SUS	1	NATURAL				
05	胶壳 HOUSING	PA	1	BLACK C				
04	接触片 CONTACT	C5210R	2	Ag CLAD				
03	胶盖 COVER	PA	1	BLACK C				
02	弹簧 SPRING	SUS	1	NATURAL				
01	胶柄 KNOB	POM	1	NATURAL				
序NO.	零件 PART	材料 MATERIAL	数量 QTY	备注 REMARKS	标号 REV	内容 DESCRIPTION	签名 SIGN.	日期 DATE
					DWG NO. ITEM3141			

TOLERANCES UNLESS OTHERWISE SPEC.		TITLE	PUSH SWITCH		ITEM NO	PS-2214-L NS PA		
UNDER 1	± 0.10	DRAWN	张渠江	2009-12-28	VERSION	A01	PAGE 1	OF 1
1 - 10	± 0.30	REVIEWED	王光云	2009-12-28	SCALE	—	UNIT	mm
OVER 10	± 0.50	APPROVED	马建和	2009-12-28	PROJECTION			

COMAX

高铭电子(惠州)有限公司
Comax Electronics(Huizhou)Co.,Ltd.