

Direct Links

Cross Reference

RoHS/LF P/N search

Document & Drawing search

Application tooling

Services

Contact us

Distributor list

Pricing request

Order samples

Literature

Brochures & catalogs

Product documentation

Technical library

Start > Search=bibs-350-3* > BIBS-350-3

BIBS-350-3



BIBS-350-3

350-10,ONE-SIDE, UNITAP

ACTIVE

Customer Drawing

RoHS compatible

Electrical division

Assistant Add to Favorites

Email Datasheet Print Datasheet

FCI Brings You More

- Contact our sales/technical support
- Sample request
- Price request

Download document

Literature

- > Oxide Inhibitor Unitap Material Safety Data Sheet
- > Power solutions Product Focus
- > Insulated Multiple Connectors Brochures
- > Aluminum Products Brochure
- > UNITAP Insulated Multiple Tap Connectors Brochure
- > Renewable Energy Products Brochure
- > EC&M Catalog
- > Connector Theory and Application Brochure

Application Tooling

- > Electrical Tooling

Specifications

General	Dimensional	Physical	Approvals / Certifications	Other Features
---------	-------------	----------	----------------------------	----------------

General	
Number of Ports	3
Dimensional	
Height (in)	2.5 in.
Length (in)	3.13 in.
Width (in)	2.32 in.
Wire Entry	Single
Hex Size (Key)	5/16 in.
Physical	
Conductor Size	250 kcmil
	4/0 AWG
	2/0 AWG
	3/0 AWG
	2 AWG
	1 AWG
	4 AWG
	1/0 AWG
	350 kcmil
	8 AWG
	10 AWG
	6 AWG
Conductor Size (Range)	10 AWG to 350 kcmi
Approvals / Certifications	
UL Listed	Yes
CSA Certified	No
Other Features	
UPC	78181013177
Keyword	unitap