

Euro-conn

product specification

SPECIFICATION

Current Rate:3 AMP

Insulation Resistance:1000M Ω Min.

Contact Resistance:20m Ω Max.

Dielectric Voltage:1000V AC for one minute

Operation Temperature:-40°C to +105 °C

Soldering Temperature:200°C / 5 Sec

MATERIAL




Insulator Material:Polyester,UL 94V-0

©Standard:P.B.T

Contact Material:Brass

Finish:Gold plated

©Standard: Gold flash all over



ORDER INFORMATION:

FH254 - **1** **XX** **DF085T** **149V**

N.ro Pin

UNITS	mm	SIZE	A4	SCALE	FIRST ANGLE PROJECTION
 Euro-conn					
					HEADER

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Arduino:](#)

[A000040](#)