


## DIMENSIONS: mm (in.)



POS.1	POS.2
ON	ON
2-3	2-1
 2 Comm. 3	 2 Comm. 3

## SWITCH FUNCTION

## Electrical Specifications:

- Contact Resistance: 10mΩ max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩ min.
- Rating: 2A / 250 VAC; 5A / 120 VAC or 28 VDC
- Dielectric Strength: 1,000 V RMS@ sea level

## Mechanical Specifications:

- Operating Temperature: -30°C to +85°C

## Note:

- RoHS Compliant by Exemption

## Materials:

- Case: Diallyl phthalate (DAP)
- Actuator: Brass, chrome plated
- Bushing: Brass, nickel plated
- Housing: Stainless steel
- Terminal/Contact: Silver plated

Toggle Switch  
108-1MS1T2B3M2QE-EVX

**Mountain**  
**Switch**

Available from Mouser Electronics

[www.mouser.com](http://www.mouser.com) 1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[108-1MS1T2B3M2QE-EVX](#)