

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190730165](#)
Status: **Active**
Description: Avikrimp™ Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 8, Length 27.71mm (1.091")

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Ring and Spade Terminals
Series [19073](#)
Comments Type II Insulated; Class 1 and 2
Mil-Spec AS25036-156, MS25036-156
Product Name Avikrimp™
Type Ring

Physical
Barrel Type Closed
Flammability 94V-0
Insulation Nylon (PA)
Material - Plating Mating Tin
Packaging Type Bag
Plating min: Mating (µin) 100
Plating min: Mating (µm) 2.5
Plating min: Termination (µin) 100
Plating min: Termination (µm) 2.5
Stud Size 8 (M4)
Wire Insulation Diameter 5.70mm (.225") max.
Wire Size AWG 10, 12
Wire Size mm² 3.30 - 5.00

Electrical
CSA LR18689
UL E32244

Material Info
Old Part Number C-828-08

Reference - Drawing Numbers
Sales Drawing SD-19073-007




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19073Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Hand Crimp Tool	0640010100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100
Hand Crimp Tool	0640011500