

Joker foot-Ring Wrench



Design: Hexagon bolt heads or nuts

Application: Foot-and-ratchet wrench, hold function by metal plate in his mouth, reduces the risk of losing screws and nuts; replaceable metal plate in his mouth secures with extra hard teeth nuts and bolts and reduces the risk of slipping; integrated end stop can prevent slipping from the screw head down and allows the application of high torque, the twin hexagonal geometry ensures the positive connection with screw or nut and thus reducing the risk of slipping; backward tilt angle of only 30 ° on the side of the mouth to avoid the time-consuming turning of the key in the screw; ratchet mechanism on the ring side with exceptionally high fine teeth of 80 teeth for flexibility in confined spaces, special forged geometry for high torque transmission and high bending stiffness; powerful chrome-molybdenum steel, nickel-chrome plating for high corrosion protection.

Code	mm	mm	mm	mm	mm	mm
05073268001	8	144	20	5,5	18	7
05073270001	10	159	22	5,5	21	7,2
05073271001	11	165	25	6,3	22	7,5
05073272001	12	170,7	26,3	6,6	25	8,5
05073273001	13	177	27,3	7	25	8,6
05073274001	14	188	29,3	7,5	28	9,2
05073275001	15	200	32,3	7,8	28,5	9,2
05073276001	16	212	35	8,2	32,7	10,5
05073277001	17	224	37,2	8,5	32,7	10,5
05073278001	18	235	39	9	33,8	11
05073279001	19	246	42	9,5	34,8	11