

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301070033](#)
Status: **Active**
Overview: [Stringlights](#)
Description: Super-Safeway Assembled Rubber Stringlight 200W 14/3 SOOW 1.52m (5.0') Lead with Guard 3.04m (10.0'), Overall Length 30.48m (100.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
 Series [130107](#)
 NEMA Configuration NEMA L5-20
 NEMA Rating Rain Tight
 Outlet None
 Overview [Stringlights](#)
 Product Name Super-Safeway
 Type String Lights
 UPC 78678879858

Physical

Cord Length - Primary 3.04m (10.0')
 Cord Length - Secondary N/A
 Depth 46.48mm (1.830")
 Duty Industrial
 Guard Included Yes
 Guard Type Steel
 Height 101.60mm (4.000")
 Length 30.48m (100.0')
 Material - Guard #8 Gauge Zinc-plated Steel
 Mounting Style Stringer
 Net Weight 17.236/kg
 Packaging Type Carton
 Socket Construction Assembled

Electrical

Bulb Type Incandescent
 Cord Type - Primary 12/3 SOOW
 Lamp Type A21
 Lamp Wattage - Maximum 200W
 Lumens 2000
 On/Off Switch No
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 310423



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130107 Series](#)