

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191640048](#)
Status: **Active**
Description: Perma-Seal™ Male Quick Disconnect Tab for 14-16 AWG Wire, Tab Size 6.35mm (.250") x .81mm (.032")

Documents:

[Product Literature \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

General

Product Family Quick Disconnects
Series [19164](#)
Product Name Perma-Seal™
Type Quick Disconnect

Physical

Barrel Type Closed
Color - Resin Natural
Flammability 94V-0
Gender Male
Glow-Wire Compliant No
Insulation NiAc™
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Zinc Chromate
Material - Plating Termination Zinc Chromate
Material - Resin Nylon
Orientation Straight
Packaging Type Bag
Plating min: Mating (µin) 200
Plating min: Mating (µm) 5
Plating min: Termination (µin) 200
Plating min: Termination (µm) 5
Tab Thickness 0.81mm (.032")
Tab Width 6.35mm (.250")
Temperature Range - Operating -55°C to +125°C
Wire Insulation Diameter 4.32mm (.170") max.
Wire Size AWG 14, 16
Wire Size mm² 1.00 - 2.50

Electrical

CSA LR18689
UL E79133
Voltage - Maximum 600V

Material Info

Old Part Number SBB-9262



Series image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[19164Series](#)

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640054500
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640054700
Hand Crimp Tool	0640014500
Hand Crimp Tool	0640014700