



Sample photo

Order symbol: PC 17/16-C3
Product nbr: 7520080

Description: Enclosure, PC
Remarks: No main cover

EAN: 6418074010179
El. number:
Finland 3422926
Denmark 8212016606
Italy 7719000

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Smoked transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Dimensions:			
	L	W	H
mm:	160	166	105
inch:	6.3	6.5	4.1
Materials:			
Material:	PC		
Base colour:	RAL 7035		
Gasket material:	EPDM		
Temperatures:			
Short term:	-40 ... 120 °C		
Continuous:	-40 ... 80 °C		
Short term:	-40 ... 250 °F		
Continuous:	-40 ... 175 °F		
Accessories:			
MP 17/16	Mounting plate		
FP 17/16	Front plate		

Rating:
Ingress Protection (EN 60529): IP 65
Impact Resistance (EN 50102): IK 08/07
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes
UV resistance: UL 508
Flammability Rating (UL 746 C 5): UL 94 5V
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 3, 3R, 12, 13
Certificates:
Underwriters Laboratories
Fimko
Europe EN 50298 1998
UL Canada
Gost R

